

Customer Information Sheet

DRAWING No.: M80-414XX98

SHEET 2 OF 2

IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

SPECIFICATIONS:**MATERIAL:**

MOULDING = GLASS-FILLED PPS, UL94V-0, BLACK


ENVIRONMENTAL:

TEMPERATURE RANGE = -55°C TO +125°C

PACKING:

BAG

FOR COMPLETE SPECIFICATION, SEE COMPONENT SPECIFICATION C005XX (LATEST ISSUE)




ORDER CODE:

M80-414XX98TOTAL No. OF POSITIONS: _____
04 TO 50
(EVEN NUMBERS ONLY)

DIMENSION	CACULATION
DIM 'A'	TOTAL No. OF CONTACTS + 10
DIM 'B'	TOTAL No. OF CONTACTS + 5
DIM 'C'	TOTAL No. OF CONTACTS - 2
EXAMPLE: HOUSING WITH 20 POSITIONS AND FIXINGS, M80-4142098	
DIM 'A' = 30.00mm, DIM 'B' = 25.00mm DIM 'C' = 18.00mm	

NOTES:

- HOUSING TO BE USED WITH M80-206005 CONACTACTS.
CONTACTS SOLD SEPERATELY.
- FOR ASSEMBLY INSTRUCTIONS, SEE IS-25.



MSP	1	12.04.17	----
NAME	ISS.	DATE	C/NOTE
APPROVED: M.PERREN			
CHECKED: S.BENNETT			
DRAWN: M.PERREN			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWINwww.harwin.com
technical@harwin.comTHIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.**TOLERANCES**X. = $\pm 1\text{mm}$
X.X = $\pm 0.50\text{mm}$
X.XX = $\pm 0.10\text{mm}$
X.XXX = $\pm 0.01\text{mm}$
ANGLES = $\pm 5^\circ$
UNLESS STATED**MATERIAL:**

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²**TITLE:**FEMALE T-CONTACT J-TEK
CRIMP CONNECTOR WITH
HEX SOCKET JACKSCREW

DRAWING NUMBER:

M80-414XX98SHT
2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

[M80-4140898](#) [M80-4143098](#) [M80-4144298](#) [M80-4143898](#) [M80-4142698](#) [M80-4143298](#) [M80-4141898](#) [M80-4144098](#) [M80-4143498](#) [M80-4142498](#) [M80-4145098](#) [M80-4144498](#) [M80-4144898](#) [M80-4140698](#) [M80-4141698](#) [M80-4141298](#) [M80-4144698](#) [M80-4140498](#) [M80-4142298](#) [M80-4143698](#) [M80-4142898](#) [M80-4141098](#) [M80-4142098](#) [M80-4141498](#)