

# Data Sheet

## Triple Output DC Power Supplies Models 1670A and 1671A

These triple output DC power supplies are ideal for general electronic servicing, school electronics labs, and powering up hobbyist's projects.

Model	1670A	1671A
<b>Output Parameters</b>		
Number of Outputs	Three (1 variable, 2 fixed)	
Range	0-30 V / 0-3 A (variable) 12 V $\pm$ 5% / 500 mA (fixed) 5 V $\pm$ 5% / 500 mA (fixed)	0-30 V / 0-5 A (variable) 12 V $\pm$ 5% / 500 mA (fixed) 5 V $\pm$ 5% / 500 mA (fixed)
<b>Constant Voltage Operation</b>		
Line Regulation	$\leq$ 0.05% + 10 mV (main) $\leq$ 1% (fixed output)	
Load Regulation	$\leq$ 0.05% + 10 mV (main) $\leq$ 1% (fixed output)	
Ripple & Noise	$\leq$ 5 mV rms	
<b>Constant Current Operation</b>		
Adjustable Current Range	5% to 100% (Main)	
Line Regulation	$\leq$ 0.4% + 10 mA	
Load Regulation	$\leq$ 0.4% + 10 mA	
Ripple & Noise	$\leq$ 10 mA rms	
<b>Metering</b>		
Display	3-digit LCDs	
Voltmeter Resolution	0.1 V	
Voltmeter Accuracy	$\pm$ (1% reading + 2 digits)	
Ammeter Resolution	0.01 A	
Ammeter Accuracy	$\pm$ (1% reading + 2 digits)	
<b>General</b>		
Overload Protection	Current limiting, Reverse polarity, Overvoltage, Short circuit	
AC Input	115/230 VAC, 50/60 Hz	
Power Consumption	165 W	265 W
Operating Temperature	0° to 40°C < 10-80% R.H.	
Storage Temperature	-15° to 70°C < 85% R.H.	
Dimensions (H x W x D)	4.9" x 8.5" x 9.5" (124 x 216 x 242 mm)	4.9" x 8.5" x 11.5" (124 x 216 x 292 mm)
Weight	10 lbs (4.5 kg)	14.3 lbs (6.5 kg)
<b>One-Year Warranty</b>		
Included Accessories	Instruction manual and spare fuse	



Model 1671A

- One variable 0 - 30 VDC,  
0 - 3 A variable section (1670A)  
0 - 5 A variable section (1671A)
- One 12 VDC fixed section
- One 5 VDC fixed section
- Constant voltage (CV) and constant current (CC) operation modes
- Short circuit and reverse polarity protection