


## Elbow cable gland

21.7xxPAzzzz

|                   |                               |
|-------------------|-------------------------------|
| Pressure screw    | Polyamide PA6 GF25            |
| Washers           | Steel, zinc-plated            |
| Sealing ring      | SBR/NBR, multiple perforation |
| Elbow             | Polyamide PA6 GF25            |
| Connecting thread | metric, as per EN 60423       |




| Properties        |  |
|-------------------|--|
| Temperature range | -20 °C<br>+100 °C  |
| Protection grade  | IP55   |
|                   | <ul style="list-style-type: none"> <li>for application in installation areas with small amounts of space due to construction dimensions</li> </ul> |



## Features

 RAL 7035

Connecting thread standard length

| A       | ØC       | L  | SW2 | H    |  VPE | Part No.     |
|---------|----------|----|-----|------|---|--------------|
| M16x1,5 | 5 - 9    | 12 | 16  | 38   | 100   | 21.716PA7035 |
| M20x1,5 | 7 - 12   | 12 | 20  | 42   | 50  | 21.720PA7035 |
| M25x1,5 | 8,5 - 15 | 12 | 25  | 48,5 | 50  | 21.725PA7035 |
| M32x1,5 | 14 - 20  | 14 | 32  | 57,5 | 25  | 21.732PA7035 |

\* The maximum sealing range is dependent on type of cable and assembling.