

## Specification Sheet

Part Number: 156-01714



Bundle can rotate to any orientation, allowing routing in any direction regardless of mounting point.

Clip is reusable, making relocation or adjustments simple.

All-in-one bundling and mounting solution reduces costs.

LOC Locking Clamp, 20–25 mm, with T50SMVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn

**Article Number** 156-01714

**Type** T50SMVCLOC20-25

**Color** Black (BK)

**Quantity Per** carton

**Product Description** HellermannTyton's 1-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.

**Short Description** LOC Locking Clamp, 20–25 mm, with T50SMVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn

**Global Part Name** T50SMVCLOC20-25-PA66HIRHSUV-BK

**Minimum Tensile Strength (Imperial)** 50.0

**Minimum Tensile Strength (Metric)** 225.0

**Length L (Imperial)** 8.3

**Length L (Metric)** 210.0

**Fixation Method** Omega Clips

**Identification Plate Position** none

**Width W (Imperial)** 0.47

**Width W (Metric)** 12.0

**Bundle Diameter Min (Imperial)** 0.79

**Bundle Diameter Min (Metric)** 20.0

**Bundle Diameter Max (Imperial)** 0.98

**Bundle Diameter Max (Metric)** 25.0

**Height H (Imperial)** 1.53

**Height H (Metric)** 38.9

**Depth D (Imperial)** 0.47

<b>Depth D (Metric)</b>	12.0
<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV
<b>Material Cable Tie</b>	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
<b>Flammability</b>	UL 94 HB
<b>Halogen Free</b>	Yes
<b>Operating Temperature</b>	-40°F to +230°F (-40°C to +110°C)
<b>Reach Compliant (Article 33)</b>	Yes
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3926909988

