



Seal, Mounting type: Plug in, Length x width: 42.8 mm, Max. cable diameter: 20 mm, IP 66, Colour: Grey

**RAL:** Ähnlich 7035

#### Business data

Packaging unit	10
Quantity unit	PC
Weight per piece (not including packaging)	28 g
Weight per piece (including packaging)	28.4 g
Unit of weight	G
Customs number	39259020
Country of origin	DE
Product description	Sealing Element

28581.6

KDS-DEG 19-20 GR

---

## Technical data

---

### Dimensions

---

Length	42.8 mm
Width	42.8 mm
Height	17.7 mm

---

### Materials

---

Material	TPE
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	90 °C
Halogen-free	✓
Silicone-free	✓

---

### Further technical data

---

Mounting type	Plug in
Degree of protection	IP66
Strain relief	✓
Cable diameter, min.	19 mm
Cable diameter, max.	20 mm
NEMA Type	4x
Number of wires	1

---

### Print

---

Colour	Grey
--------	------

---

### Environmental Product Compliance

---

REACH Conform	yes
REACH Reference date	2021-07-08
REACH Candidate Substance Note	No
RoHS Conform	yes

---

28581.6

KDS-DEG 19-20 GR

---

## Approvals

---

### Standards and regulations

---

Standards / specifications	Strain relief complying with DIN EN 62444
----------------------------	-------------------------------------------

---

### cUL Recognized

---

cUL approval	C22.2 No. 14-18
--------------	-----------------

---

cUL Recognized	yes
----------------	-----

---

### UL Recognized

---

UL approval	UL 508A
-------------	---------

---

UL Recognized	yes
---------------	-----

---

---

## Media

---



# Data sheet

28581.6

KDS-DEG 19-20 GR



---

## Accessories

---

28581.6

KDS-DEG 19-20 GR

## Inlays



Cable entry, Inlay, Mounting type: Plug in, IP 66, Colour: Black

### detail.dataSheet.generalOrderData

Product number:	detail.dataSheet.productName	GTIN (EAN)	detail.dataSheet.
28516.4	KDS-Inlay 1 BK	4044211210847	500 ST



Cable entry, Inlay, Mounting type: Plug in, IP 66, Colour: Black

### detail.dataSheet.generalOrderData

Product number:	detail.dataSheet.productName	GTIN (EAN)	detail.dataSheet.
28517.4	KDS-Inlay 2 BK	4044211210854	500 ST



Cable entry, Inlay, Mounting type: Plug in, IP 66, Colour: Black

### detail.dataSheet.generalOrderData

Product number:	detail.dataSheet.productName	GTIN (EAN)	detail.dataSheet.
28518.4	KDS-Inlay 4 BK	4044211210861	500 ST

Creation date 29.08.2021 19:34:30  
Subject to technical changes


28581.6

KDS-DEG 19-20 GR

---

## Inlays

---



Cable entry, Inlay, Mounting type: Plug in, IP 66, Colour: Black

---

detail.dataSheet.generalOrderData

Product number:	detail.dataSheet.productName	GTIN (EAN)	detail.dataSheet
28519.4	KDS-Inlay 6 BK	4044211210014	500 ST

---

28581.6

KDS-DEG 19-20 GR

## Screw frame



Cable entry with foamed-in seal, Mounting type: Screws, Length: 153 mm, Width: 70 mm, IP 66, Colour: Black

### detail.dataSheet.generalOrderData

Product number:	detail.dataSheet.productName	GTIN (EAN)	detail.dataSheet.
28504.4	KDS-SR 10/24 BK	4044211210809	500 ST



Cable entry with foamed-in seal, Mounting type: Screws, Length: 106 mm, Width: 70 mm, IP 66, Colour: Black

### detail.dataSheet.generalOrderData

Product number:	detail.dataSheet.productName	GTIN (EAN)	detail.dataSheet.
28500.4	KDS-SR 6/10 BK	4044211210021	500 ST



Cable entry with foamed-in seal, Mounting type: Screws, Length: 126 mm, Width: 70 mm, IP 66, Colour: Black

### detail.dataSheet.generalOrderData

Product number:	detail.dataSheet.productName	GTIN (EAN)	detail.dataSheet.
28502.4	KDS-SR 8/16 BK	4044211210786	500 ST

Creation date 29.08.2021 19:34:30  
Subject to technical changes



28581.6

KDS-DEG 19-20 GR

---

## Screw frame

---



Cable entry with foamed-in seal, Mounting type: Screws, Length: 81 mm, Width: 70 mm, IP 66, Colour: Black

---

detail.dataSheet.generalOrderData


Product number:	detail.dataSheet.productName	GTIN (EAN)	detail.dataSheet
28506.4	KDS-SR 1-4 BK	4044211210823	500 ST

---

28581.6

KDS-DEG 19-20 GR


## Locking frame



Inner locking frame, Length: 80 mm, Height: 11.5 mm, Colour: Black

### detail.dataSheet.generalOrderData


Product number:	detail.dataSheet.productName	GTIN (EAN)	detail.dataSheet.
28507.4	KDS-IVR 1-4 BK	4044211210830	500 ST



Inner locking frame, Length: 105 mm, Height: 11.5 mm, Colour: Black

### detail.dataSheet.generalOrderData

Product number:	detail.dataSheet.productName	GTIN (EAN)	detail.dataSheet.
28501.4	KDS-IVR 6/10 BK	4044211210779	500 ST



Inner locking frame, Length: 125 mm, Height: 11.5 mm, Colour: Black

### detail.dataSheet.generalOrderData

Product number:	detail.dataSheet.productName	GTIN (EAN)	detail.dataSheet.
28503.4	KDS-IVR 8/16 BK	4044211210793	500 ST

Creation date 29.08.2021 19:34:30  
Subject to technical changes


28581.6

KDS-DEG 19-20 GR

---

## Locking frame

---



Inner locking frame, Length: 152 mm, Height: 11.5 mm, Colour: Black

---

### detail.dataSheet.generalOrderData

Product number:	detail.dataSheet.productName	GTIN (EAN)	detail.dataSheet
28505.4	KDS-IVR 10/24 BK	4044211210816	500 ST

---