


Specification Sheet

Part Number: FTB



Can be cut to length with scissors, eliminating waste and keeping stock to a minimum.

Available in 9 sizes, for thicknesses from .016" to .512", insuring proper fit.

Grommet, Panel Thickness 0.051"-0.083", PTFE, Natural, 9.7ft/pkg

Article Number 251-30209

Type G51TB

Color Natural (NA)

Quantity Per reel

Product Description HellermannTyton's Flexiform grommet is a unique, continuous wire protection product which fits easily in all shapes and sizes of holes without the aid of tools or adhesives. Flexiform grommet can be used on any type of material including wood, steel, aluminum, plexiglass, and glass.

Short Description Grommet, Panel Thickness 0.051"-0.083", PTFE, Natural, 9.7ft/pkg

Global Part Name G51TB-PTFE-NA

Length L (Imperial)	9.7
Variant	Open
Width W (Imperial)	0.181
Width W (Metric)	4.6
Height H (Imperial)	0.169
Height H (Metric)	4.3
Panel Thickness Min (Imperial)	0.051
Panel Thickness Max (Imperial)	0.083
Panel Thickness Min (Metric)	1.30
Panel Thickness Max (Metric)	2.10
Material	Polytetrafluoroethylene (PTFE)
Material Shortcut	PTFE
US MIL SPEC	MS21266-2T
Flammability	UL 94 V-0

Halogen Free	No
Operating Temperature	-76°F to +500°F (-60°C to +260°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	9.7
Package Quantity (Metric)	3
Customs Number	3926909988

© 2021 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)