

## Specification Sheet

Part Number: 126-00049



Two piece assembly allows the mount to slide along the strap ensuring proper orientation.

Arrowhead style mount provides low insertion and high extraction force.

Arrowhead disc protects against dirt and other impurities.

1-Pc Cable Tie/Arrowhead Mount w/Wings, 6"L, 50lb, 0.24 - 0.26" Hole Dia, PA66HIRHSUV, Black, 500/bag

**Article Number** 126-00049

**Type** T50SSFMM

**Color** Black (BK)

**Quantity Per** bag

**Product Description** Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

**Short Description** 1-Pc Cable Tie/Arrowhead Mount w/Wings, 6"L, 50lb, 0.24 - 0.26" Hole Dia, PA66HIRHSUV, Black, 500/bag

**Global Part Name**

T50SSFM-PA66HIRHSUV-BK

**Minimum Tensile Strength (Imperial)**

50.0

**Minimum Tensile Strength (Metric)**

225.0

**Length L (Imperial)**

6.3

**Length L (Metric)**

160.0

**Fixation Method**

Arrowhead

**Identification Plate Position**

none

**Releasable Closure**

No

**Tie Closure**

plastic pawl

**Variant**

Inside Serrated

**Width W (Imperial)**

0.18

**Width W (Metric)**

4.6

**Bundle Diameter Min (Imperial)**

0.13

**Bundle Diameter Min (Metric)**

3.2

**Bundle Diameter Max (Imperial)**

1.38

**Bundle Diameter Max (Metric)**

35.0

<b>Height H (Imperial)</b>	.20
<b>Height H (Metric)</b>	5.60
<b>Panel Thickness Min (Imperial)</b>	0.028
<b>Panel Thickness Max (Imperial)</b>	0.12
<b>Panel Thickness Min (Metric)</b>	0.7
<b>Panel Thickness Max (Metric)</b>	3.0
<b>Mounting Hole Diameter D (Imperial)</b>	0.24 - 0.26
<b>Mounting Hole Diameter D (Metric)</b>	6.0 - 6.6 mm
<b>Mounting Hole Diameter D Min (Imperial)</b>	0.24
<b>Mounting Hole Diameter D Max (Imperial)</b>	0.25
<b>Mounting Hole Diameter D Max (Metric)</b>	6.6
<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)

<b>Reach Compliant (Article 33)</b>	Yes
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	500
<b>Package Quantity (Metric)</b>	500
<b>Customs Number</b>	3926909988