

Specification Sheet

Part Number: TAG10T2-100B

HellermannTyton Self-Laminating Labels come on rolls on a standard 3" core for easy loading into a printer or caddy.

Labels are conformable so that they can bend around small gauge wires and tight bends without coming loose over time.



Labels are UL recognized for indoor and outdoor use to expand application options.

HellermannTyton thermal transfer labels work in any thermal transfer printer so that the use always has options to get labels printed without being locked into a single vendor.

Article Number 596-00002

Type TAG10T2

Color White (WH)

Quantity Per roll

Product Description HellermannTyton thermal transfer self-laminating labels are a conformable vinyl film with a white printable surface followed by a clear tail that laminates the printed text when applied to a wire or cable. The labels are UL recognized for indoor and outdoor use with an aggressive acrylic adhesive that allows the label to bond to large and small diameter wires.

Short Description	Thermal Transfer Labels, Self-Laminating, 2.0" x .75" x 2.25", 2 Across, VL, White, 2500/roll
Global Part Name	TAG10T2-100B-WH
Length L (Imperial)	2.0
Length L (Metric)	50.8
Width W (Imperial)	2.0
Width W (Metric)	50.8
Bundle Diameter Min (Imperial)	0.216
Bundle Diameter Min (Metric)	5.5
Bundle Diameter Max (Imperial)	0.476
Bundle Diameter Max (Metric)	12.1
Thickness T (Metric)	25
Width of Liner (Metric)	98.42
Width of Liner (Imperial)	3.875
Material	Type 100B (100B)

Material Shortcut	100B
Adhesive	Acrylic
Halogen Free	No
Adhesive Operating Temperature	-51°F to +200°F (-46°C to +93°C)
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-Recognized
UL Recognized (US)	Yes
Package Quantity (Imperial)	2500
Package Quantity (Metric)	2500
Customs Number	3919102055
Labels per Column	1
Labels per Row	2

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)