



Wi-Fi 6/ 6E TRIPLE BAND EMBEDDED ANTENNA

Part Numbers: 2108891-1

FEATURES & BENEFITS

- WiFi 6, also including WiFi 6E new 6GHz band, Bluetooth, ZigBee
- Tab mounting with plated through holes
- Global Frequency coverage
- Minimal keep out zone requirement
- Performance dependent on ground plane size and design.

SPECIFICATIONS


Frequency Range (MHz)	2400-2500	5150-5875	5925-7125
VSWR	< 2.0:1	< 2.0:1	< 2.0:1
Average Efficiency	60%	59%	62%
Peak Gain	1.3dBi	3.4dBi	4.3dBi
Average Gain	-2.2dBi	-2.3dBi	-2.2dBi
Power Handling	10 Watt cw		
Feed Point Impedance	50 ohms unbalanced		
Polarization	Linear		
Size	30.0 mm x 10.0 mm x 0.78 mm		
Weight	< 0.5 g		
Mounting	TAB mounting with plated through holes		
Operating Temperature	-40 to +85°C		
Storage Temperature	-40 to +85°C		
Hazardous Materials	A certificate of conformance is available from the product page on TE website.		
Data measured in free space and on reference ground plane of 29.5 mm length and 29.0 mm width, application data might vary			

RF DATA




Data measured in free space and on reference ground plane of 29.5 mm length and 29.0 mm width, application data might vary

RADIATION PATTERN




Data measured in free space and on reference ground plane of 29.5 mm length and 29.0 mm width, application data might vary

Standard Antenna Solutions




Data measured in free space and on reference ground plane of 29.5 mm length and 29.0 mm width, application data might vary

KEEP OUT AREA




NOTES :1. Area in blue above indicates Keep Out Area. 2. For more information please call TE.

Dimensions: mm Diagram is not to scale



PACKAGING



TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

For phone numbers in other countries, go to te.com/support-center

te.com

TE Connectivity, TE Connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2020 TE Connectivity Ltd. family of companies All Rights Reserved.

12/2020



