

DVI Single Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 18-in. (45.72 cm)

MODEL NUMBER: P561-18N



Highlights

- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Resolutions up to 1920 x 1200
- High Speed Digital Transmission to 4.95Gbps

System Requirements

- Monitor with DVI, and CPU with a DVI video card

Package Includes

DVI Single Link TMDS cable - DVI-D, M/M, 18-in.

Features

- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Single Link digital signaling for transmission speeds to 4.95Gbps and 1920 x 1200 resolution
- Gold plated contacts ensure excellent conductivity
- Meets DVI DDWG Standard
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projectors

Specifications

OVERVIEW	
UPC Code	037332185990
Product Type	Passive
Technology	DVI
PHYSICAL	
Color	Black
Cable Length (ft.)	1.5
Cable Length (m)	0.5
Cable Length (in.)	18
Cable Length (cm)	45.72
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (kg)	0.13
Shipping Weight (lbs.)	0.28
CONNECTIONS	
Side A - Connector 1	DVI-D SINGLE LINK (MALE)
Side B - Connector 1	DVI-D SINGLE LINK (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>