

HUBER+SUHNER® DATA SHEET

Within Series Adapter: 34_SMA-50-0-100/111_N



Description

Bulkhead adaptor jack/jack
SMA-26.5GHz jack (female) / SMA-26.5GHz jack (female)

Interface standards
SUHNER-SMA-26.5GHz



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 26.5 GHz
Electrical Length 25.72 mm +/- 0.1

Mechanical Data

Number of matings 500
Weight 0.0041 kg

Environmental Data

Operating Temperature -65 °C to 125 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts (SMA-26.5GHz)

Centre contact	Copper Beryllium Alloy
Outer contact	Copper Beryllium Alloy
Body	Copper Beryllium Alloy
Insulator	PFA / PTFE

Piece Parts (SMA-26.5GHz)

Centre contact	Copper Beryllium Alloy
Outer contact	Copper Beryllium Alloy
Body	Copper Beryllium Alloy
Insulator	PFA / PTFE

Surface Plating

Gold Plating (Nickel underplated)
Gold Plating (Nickel underplated)
Gold Plating (Nickel underplated)

Surface Plating

Gold Plating (Nickel underplated)
Gold Plating (Nickel underplated)
Gold Plating (Nickel underplated)

Related Documents

Mounting hole DOU-00008731

Ordering Information

Single package 34_SMA-50-0-100/111_NE

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions