


Category:

MALE HEADER

Product:

STRIP HEADERS

Male header straight



FEATURES:

Breakable header, insulator profile 2.6mm
Pin side dimension 0.6mm

MATERIAL:

Housing: High temperature thermoplastic UL94 V0
Contact: Phosphor bronze.

ELECTRICAL:

Current rating: 4A maxi.
Dielectric withstanding: 1000 V
Insulation resistance: 10000 M Ω mini

MECHANICAL:

Temperature rating: -55°C to +125°C
Pc board Hole diameter \varnothing 1 mm.

PACKAGING:

Recyclable cardboard boxes.

PRODUCT CODE

A	B	C	D
471	xxxx	1xx	4x0

Version	A	B	C
0543	9.2	3.3	3.3
0290	10.2	4.5	3.1
0358	11.2	5.4	3.2
1955	11.2	5.8	2.8
1956	12.4	5.8	4
0334	12.4	6.8	3
2801	12.9	7.3	3
0369	13.8	7.7	3.5
2035	13.8	8.1	3.1
0302	14.5	7	4.9
2754	14.5	8.8	3.1
0385	15.1	8	4.5
2286	15.1	9.3	3.2
2581	16.3	10.9	2.8
0575	17.7	12	3.1
2673	19.5	13.7	3.2
0211	22	15.6	3.8
2643	22	16.4	3
2003	25.8	20.2	3
0307	30.8	22.4	5.8
2804	30.8	25.2	3


CODE LEGEND

- B** Version
- C** Number of contacts from 01 to 40.
- D** Plating
 - 0 Gold
 - 0.2 μ m over Ni 1.27 μ m
 - 4 Tin 4 μ m over Ni 1.27 μ m
 - Other platings on demand.

Pitch 2.54 mm

www.stelvio-kontek.com
+39.0341.265411





NOTE