


SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN)

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)



- NOTE:
- 1 DA MISURARSI CON LA MOLLA IN POSIZIONE ORIZZONTALE
(Measured when spring is horizontal)
 - 2 ADATTO PER TERMINALE MASCHIO CON FORO, SECONDO TABELLA FIAT 91319 FOGLIO 2 (TIPO A) (Suitable for Tab 0.8 THK with hole)
 - 3 MASSIMA SCIABOLATURA AMMESSA: 18 mm PER METRO (Camber: 18mm/m)
 - 4 SENSO DI USCITA DEL TERMINALE DALLA BOBINA. (P.N. -2)
(Direction off top of reel)
 - 5 ONLY WELDED SPLICES ALLOWED

5	STAGNATO (Tin Plated)	(Brass) OTTONE OT 70	281828-2
	---	(Brass) OTTONE OT 70	281828-1
FINITURA / COLORE (FINISH / COLOUR)		MATERIALE (MATERIAL)	NUMERO (PART NUMBER)

CUSTOMER DWG. FOR REFERENCE ONLY DISEGNO PER CLIENTE SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION 18

© COPYRIGHT 1986 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING

TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)	DIAM. ISOLANTE (INS. DIA. RANGE)	RANGO FILO (WIRE RANGE)	SCALA (SCALE)
±0.3	3.6-4.3 mm	2.5-4.0 mm ²	-

ANGOLI
CANGLED

± 2°

TE TE Connectivity

DESCRIZIONE
(DESCRIPTION) (MARK I)

POSITIVE LOCK REC.

REV.	REVISIONI (REVISION RECORD)	DIS. DATA (DATES)	APP. APP. 2
A3	REVISED PER ECR-20-012400	SS	24 SEP 2020
A2	ECR-16-009345	L.P.	19 JUL 16
A	In Produzione	ES	3-XII 87

LOC. SIZE	NUMERO (CONS NO)	REV.	FOGLIO (SHEET)
A3	C-281828	A3	01

DISTRIBUZIONE
(PRINT DIST.)