



- 1 - 1 FEET ±1 INCH
- 2 - 2 FEET ±1 INCH
- 3 - 3 FEET ±1 INCH
- 4 - 4 FEET ±1 INCH
- 5 - 5 FEET ±1 INCH
- 6 - 6 FEET ±2 INCH
- 7 - 7 FEET ±2 INCH
- 8 - 8 FEET ±2 INCH
- 9 - 9 FEET ±2 INCH
- 10 - 10 FEET ±2 INCH

- BK - BLACK
- R - RED
- O - ORANGE
- Y - YELLOW
- G - GREEN
- BL - BLUE
- P - PURPLE
- WH - WHITE

NOTES:

0B

1. CABLE: BELDEN 1505A OR ENGINEERING APPROVED EQUIVALENT VIDEO CABLE, 75 OHM MATTE PVC JACKET - SEE CHART FOR COLOR
2. PLUG: VIDEO UHD PLUG, MID SIZE, BRASS, NICKEL PLATED
3. BOOT: PLASTIC UL94-V0, GREY COLOR ON ALL CABLES.
4. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
					SIZE	WIDTH	MULT	LBS/M	TEMPER	
					FINISH			MATERIAL		
					SPEC No.			SPEC No.		
					FIRST USED ON		SCALE 2:1			
					DATE DRAWN	BY	CHKD	APVD		
					8-9-16	SRC	8-9-16	*		
							SRC	*		
0B	CHG NUMBER	11-8-16	SRC	SRC						
REV	ECO NUMBER	DATE	BY	APVD						
REVISIONS					DO NOT SCALE DRAWING					
					NAME			PART No.		
					MID SIZE VIDEO PLUG PATCH CORD, RoHS			VMP1__UHD - VMP10__UHD		
										REV
										0B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[VMP2BKX](#) [VMP10BK](#) [VMP10BL](#) [VMP10GN](#) [VMP10GY](#) [VMP10O](#) [VMP10P](#) [VMP10R](#) [VMP10Y](#) [VMP1BK](#)
[VMP1BL](#) [VMP1GN](#) [VMP1GY](#) [VMP1O](#) [VMP1P](#) [VMP1R](#) [VMP1Y](#) [VMP2BL](#) [VMP2GN](#) [VMP2GY](#) [VMP2O](#) [VMP2P](#)
[VMP2R](#) [VMP2Y](#) [VMP3BK](#) [VMP3BL](#) [VMP3GN](#) [VMP3GY](#) [VMP3O](#) [VMP3P](#) [VMP3R](#) [VMP3Y](#) [VMP4BK](#) [VMP4BL](#)
[VMP4GN](#) [VMP4GY](#) [VMP4O](#) [VMP4P](#) [VMP4R](#) [VMP4Y](#) [VMP5BK](#) [VMP5BL](#) [VMP5GN](#) [VMP5GY](#) [VMP5O](#) [VMP5P](#)
[VMP5R](#) [VMP5Y](#) [VMP6BK](#) [VMP6BL](#) [VMP6GN](#) [VMP6GY](#) [VMP6O](#) [VMP6P](#) [VMP6R](#) [VMP6Y](#) [VMP7BK](#) [VMP7BL](#)
[VMP7GN](#) [VMP7GY](#) [VMP7O](#) [VMP7P](#) [VMP7R](#) [VMP7Y](#) [VMP8BK](#) [VMP8BL](#) [VMP8GN](#) [VMP8GY](#) [VMP8O](#) [VMP8P](#)
[VMP8R](#) [VMP8Y](#) [VMP9BK](#) [VMP9BL](#) [VMP9GN](#) [VMP9GY](#) [VMP9O](#) [VMP9P](#) [VMP9R](#) [VMP9Y](#) [VMP2GYUHD](#)
[VMP3RUHD](#) [VMP2BKUHD](#) [VMP2GNUHD](#) [VMP3BKUHD](#) [VMP5BKUHD](#) [VMP2RUHD](#) [VMP8BKUHD](#)