



Part No.	Cable Type	Capacitance PF/ft.	Nominal Impedance	Cable Color	Cable O. D.
BNC-C-XX	RG58C/U	30.8	50 Ohms	Black	0.195"

## MATERIALS:

BNC Body: Brass, Tarnish Resistant Plating, Center Contact: Gold Plated Brass  
 Dielectric: PTFE

## RATINGS:

Operating Voltage: Shield-Earth: 33VRMS/70VDC Max  
 Inner Conductor/Shield: 500VRMS Max  
 Operating Temperature: +80°C (+176°F) Max  
 Nominal Impedance: 50 Ohms

## ORDERING INFORMATION: Model BNC-C-XX

XX = Cable Length in inches, length tolerance:  $\pm 0.5''$   
 Standard Lengths: 18'', 24'', 36'', 48'', 60''  
 Upon request, other lengths may be quoted.

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.  
 Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[BNC-C-36](#) [BNC-C-72](#) [BNC-C-48](#) [BNC-C-18](#) [BNC-C-24](#) [BNC-C-60](#) [BNC-C-96](#)