


SPECIALTY PRODUCTS

ATO® Diode



MINI® Diode



Specifications

Operating Temp.: -40°C to +85°C
 Power Rating: 1/4 W Max
 Body Material: Thermoplastic
 Term. Material: C.R.S. (Ni/Zn Plated)
 Term. Retention: 25 N

Part Number	Type	Current Rating	Peak Inverse Voltage	Housing Color	Part Quantity
02400103_	ATO	1 A	400 Volts	Black	Z = 1500 / LXN = 50
02400104P	MINI	1 A	400 Volts	Black	2000
02400110P	MINI	1 A	400 Volts	Black	2000
02400113P	MINI	1 A	400 Volts	Black	2000
02400115P	MINI	1 A	1000 Volts	Green	2000
02400119P	MINI	1 A	400 Volts	Black	2000
02400120P	MINI	1.5 A	400 Volts	Brown	2000

* 1 A Diode in ATO® size housing. The cathode connector is rotated 90°

ATO® Resistor



MINI® Resistor



Specifications

Body Material: Thermoplastic
 Term. Material: C.R.S. (Ni/Zn Plated)
 Term. Retention: 25 N

Operating Temp for ATO is -20°C to +85°C
 Power Rating: 1/4 W Max

Operating Temp.: -40°C to +85°C
 MINI Resistor Power Rating is up to 1/2 W

Part Number	Type	Current Rating	Wattage	Housing Color	Part Quantity
02400105Z	ATO	10K ohm	¼ Watt	White	1500
02400116P	ATO	750 ohm	¼ Watt	Yellow	2000
02400106P	MINI	620 ohm	½ Watt	Grey	2000
02400107P	MINI	121 ohm	½ Watt	Grey	2000
02400108P	MINI	5.1K ohm	¼ Watt	Blue	2000
02400111P	MINI	16.9 ohm	¼ Watt	Red	2000
02400112P	MINI	121 ohm	½ Watt	Green	2000
02400114P	MINI	240 ohm	½ Watt	Green	2000
02400118P	MINI	500 ohm	½ Watt	Grey	2000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[02400113P](#) [02400104P](#) [02400106P](#) [02400103Z](#) [02400118P](#) [02400105Z](#) [02400113XP](#) [02400120P](#) [02400107P](#)
[02400108P](#) [02400115P](#) [02400117P](#) [02400119P](#) [02400114P](#) [02400110P](#)