

Product data sheet

Specifications



Easy PDU, Basic, ZeroU, 16A, 230V, (20)C13 & (4)C19; IEC309

EPDU1116B

Overview

Lead time Usually in Stock

General

Provided equipment Installation guide
Toolless mounting kit
Vertical mounting brackets

Physical

Cable length 3.00 m

Colour Black

Depth 4.44 cm

Height 90.2 cm

Net weight 2.2 kg

Width 6.2 cm

Input

Input current limits 16 A

Load capacity 3680 VA

Network frequency 50/60 Hz

Plug standard IEC 60309 16 A 2P + E

Input voltage 200 V
208 V
230 V

Output

Number of power socket outlets 20 IEC 60320 C13
4 IEC 60320 C19

Conformance

Product certifications CE
TÜV

Environmental

Ambient air temperature for operation 0...45 °C

Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Package 1 Weight	2.98 kg
Package 1 Height	132 cm
Package 1 width	16 cm
Package 1 Length	11 cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------