

Product data sheet

Specifications



Easy PDU, Basic, ZeroU, 32A, 230V, (21) SCHUKO; IEC309

EPDU1132B-SCH

Overview

Lead time Usually in Stock

General

Provided equipment Installation guide
Toolless mounting kit
Vertical mounting brackets

Physical

Cable length 3.00 m
Colour Black
Depth 4.44 cm
Height 150.6 cm
Net weight 4.3 kg
Width 6.2 cm

Input

Input current limits 32 A
Load capacity 7360 VA
Network frequency 50/60 Hz
Plug standard IEC 60309 32 A 2P + E
Input voltage 200 V
208 V
230 V

Output

Number of power socket outlets 21 Schuko CEE 7

Conformance

Product certifications CE
TÜV

Environmental

Ambient air temperature for operation -5...45 °C

Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Package 1 Weight	5.5 kg
Package 1 Height	166 cm
Package 1 width	16 cm
Package 1 Length	11 cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------