

Product data sheet

Specifications



Easy PDU, Basic, Zero U, 11 kW, 230V, (36) C13 & (6) C19 ; IEC309

EPDU1216B

Overview

Lead time	Usually in Stock
-----------	------------------

Physical

Cable length	1.98 m
Colour	Black
Depth	4.44 cm
Height	150.6 cm
Net weight	3.08 kg
Width	6.2 cm

Input

Input current limits	16 A
Load capacity	11000 VA
Network frequency	50/60 Hz
Plug standard	IEC 60309 16 A 3P + N + PE
Input voltage	400 V 3 phases

Output

Number of power socket outlets	36 IEC 60320 C13 6 IEC 60320 C19
--------------------------------	-------------------------------------

Conformance

Product certifications	CE TÜV EAC RCM
------------------------	-------------------------

Environmental

Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C

Storage Relative Humidity	5...95 %
----------------------------------	----------

Storage altitude	0.00...15240.00 m
-------------------------	-------------------

Packing Units

Package 1 Weight	4.28 kg
-------------------------	---------

Package 1 Height	166 cm
-------------------------	--------

Package 1 width	16 cm
------------------------	-------

Package 1 Length	11 cm
-------------------------	-------

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
--------------------------	--

Mercury free	Yes
---------------------	-----

RoHS exemption information	Yes
-----------------------------------	---------------------

Contractual warranty

Warranty	1 year repair or replace
-----------------	--------------------------
