

Product data sheet

Specifications



Easy PDU, Basic, Zero U, 22 kW, 230V, (30) C13 & (12) C19 ; IEC309

EPDU1232B

Overview

Lead time Usually in Stock

General

Provided equipment Installation guide
Toolless mounting kit
Vertical mounting brackets

Physical

Cable length 2.00 m
Colour Black
Depth 4.44 cm
Height 179.4 cm
Net weight 5.14 kg
Width 6.2 cm

Input

Input current limits 32 A
Load capacity 22000 VA
Network frequency 50/60 Hz
Plug standard IEC 60309 32 A 3P + N + PE
Input voltage 400 V 3 phases

Output

Number of power socket outlets 30 IEC 60320 C13
12 IEC 60320 C19

Conformance

Product certifications CE
TÜV
EAC
RCM

Environmental

Ambient air temperature for operation -5...45 °C

| | |
|-------------------------------------|-------------------|
| Relative humidity | 5...95 % |
| Operating altitude | 0...10000 ft |
| Ambient air temperature for storage | -25...65 °C |
| Storage Relative Humidity | 5...95 % |
| Storage altitude | 0.00...15240.00 m |

Packing Units

| | |
|------------------|--------|
| Package 1 Weight | 6.2 kg |
| Package 1 Height | 195 cm |
| Package 1 width | 16 cm |
| Package 1 Length | 11 cm |

Offer Sustainability

| | |
|----------------------------|--|
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |

Contractual warranty

| | |
|----------|--------------------------|
| Warranty | 1 year repair or replace |
|----------|--------------------------|