


# HRC cartridge fuses



Technical data and dimensions **see e-catalogue**

Pack	Cat.Nos.		<b>Cylindrical type gG</b>				
			Conform to EN 60269-1, IEC 60269-1 and 2 Veritas approved				
			<b>8 x 32 (previously 8.5 x 31.5)</b>				
	Without indicator	With indicator	Rating (Amps)	Voltage ~ (Volts)	Rupture capacity (Amps)		
10	0 123 01		1	400	20000		
10	0 123 02	0 124 02	2				
10	0 123 04	0 124 04	4				
10	0 123 06	0 124 06	6				
<b>10/100</b>	0 123 10		10				
10		0 124 10	10				
<b>10/100</b>	0 123 16	0 124 16	16				
	Without indicator	With indicator	<b>10 x 38 HRC</b>				
10	0 133 94		0.5	500	100000		
10	0 133 01		1				
10	0 133 02	0 134 02	2				
10	0 133 04	0 134 04	4				
10	0 133 06	0 134 06	6				
10	0 133 08	0 134 08	8				
10	0 133 10	0 134 10	10				
10	0 133 16	0 134 16	16				
10	0 133 20	0 134 20	20				
10	0 133 25	0 134 25	25				
	Without striker	With striker	<b>14 x 51 HRC</b>				
10	0 143 06		6	500	100000		
10	0 143 10		10				
10	0 143 16	0 145 16	16				
10	0 143 20	0 145 20	20				
10	0 143 25	0 145 25	25				
10	0 143 32	0 145 32	32				
10	0 143 40	0 145 40	40				
10	0 143 50 <sup>1</sup>	0 145 50 <sup>1</sup>	50				
	Without striker	With striker	<b>22 x 58 HRC</b>				
10	0 153 16		16			500	100000
10	0 153 20		20				
10	0 153 25		25				
10	0 153 32		32				
10	0 153 40		40				
10	0 153 50	0 155 50	50				
10	0 153 63	0 155 63	63				
10	0 153 80	0 155 80	80				
10	0 153 96	0 155 96	100				
10	0 153 97 <sup>1</sup>	0 155 97 <sup>1</sup>	125	400			

Pack	Cat.Nos.		<b>Cylindrical type aM (motor rated)</b>			
			Conform to EN 60269-1, IEC 60269-1 and 2 Veritas approved			
			<b>8 x 32 (previously 8.5 x 31.5)</b>			
	Without indicator		Rating (Amps)	Voltage ~ (Volts)	Rupture capacity (Amps)	
10	0 120 04		4	400	20000	
10	0 120 06		6			
10	0 120 08		8			
10	0 120 10		10			
	Without indicator		<b>10 x 38 HRC</b>			
			0.50	500	100000	
10	0 130 95		1			
10	0 130 01		2			
10	0 130 02		4			
10	0 130 04		6			
10	0 130 06		8			
10	0 130 08		10			
10	0 130 10		12			
10	0 130 12		16			
10	0 130 16		20			400
10	0 130 20 <sup>2</sup>		25	400		
	Without striker	With striker	<b>14 x 51 HRC</b>			
10		0 141 02	2	500	100000	
10		0 141 04	4			
10		0 141 06	6			
10		0 141 08	8			
10	0 140 10	0 141 10	10			
10	0 140 12	0 141 12	12			
10	0 140 16	0 141 16	16			
10	0 140 20	0 141 20	20			
10	0 140 25	0 141 25	25			
10	0 140 32	0 141 32	32			
10	0 140 40	0 141 40	40	400		
10	0 140 50 <sup>1</sup>	0 141 50 <sup>1</sup>	50	400		
	Without striker	With striker	<b>22 x 58 HRC</b>			
10	0 150 25	0 151 25	25	500	100000	
10	0 150 32	0 151 32	32			
10	0 150 40	0 151 40	40			
10	0 150 50	0 151 50	50			
10	0 150 63	0 151 63	63			
10	0 150 80	0 151 80	80			
10	0 150 96	0 151 95	100			
10	0 150 97	0 151 97	125			400

Pack	Cat.Nos.	<b>Neutral links</b>
10	0 123 00	8 x 32 (previously 8.5 x 31.5)
10	0 133 00	10 x 38
10	0 143 00	14 x 51
10	0 153 00	22 x 58



For technical data and dimensions, **see e-catalogue**

1: Overrating described by standards  
2: Overrating not described by standards