




1 2 3 4 5 6 7

LENGTH



① Order code: A-MC~~SS~~PP60XXX : color Grey



order lengths in meter:
0.5, 1, 2, 3, 5, 7, 10, 15, 20, 30

① Order code: A-MC~~SS~~SP60XXX/X
order lengths in meter:
0.5, 1, 2, 3, 5, 7, 10, 15, 20, 30
order color: (R) Red, (Y) Yellow,
(G) Green, (B) Blue

② Tolerance

Length Code	Length(meter)	Max-M	Min-M
005	0.5	+0.03	-0.025
010	1	+0.04	-0.035
020	2	+0.06	-0.06
030	3	+0.09	-0.09
050	5	+0.15	-0.15
070	7	+0.21	-0.21
100	10	+0.3	-0.3
150	15	+0.45	-0.45
200	20	+0.6	-0.6
300	30	+0.9	-0.9

Electrical test:
Open/Short/intermittence: 100%



NO.	NAME.	QTY	DATE	NAME
④	AL-Foil	2	19.08.2022	Luca
④	Molding PVC	2	01.02.2016	Joanna
④	RJ45 CONN	2	19.08.2022	Luca
④	CABLE	1		

SPECIFICATION
Customer-No. ASSMANN WSW-No. A-MC~~SS~~PP60XXX/X
Drawing-No. ASS 7542 CA rev06
Replace Sheet

Scale	FREE
TOLERANCE	

RoHS compliant
Unit: mm

Scale	FREE
TOLERANCE	
DIM	TOL
Angle	TOL

Id.	Modification	Date	Name
①	Add Grey color order code	11.08.2016	Ray
②	Clarify the tolerance	23.08.2018	Segal
③	Update the cable description	01.11.2018	Segal
④	Change the plant	12.04.2022	Luca
⑤	Add length code	29.06.2022	Luca

Scale	FREE
TOLERANCE	
DIM	TOL
Angle	TOL

Id.	Modification	Date	Name
①	Add Grey color order code	11.08.2016	Ray
②	Clarify the tolerance	23.08.2018	Segal
③	Update the cable description	01.11.2018	Segal
④	Change the plant	12.04.2022	Luca
⑤	Add length code	29.06.2022	Luca