



NEW CF SERIES

SWITCHCRAFT QUALITY JACKS IN A RUGGED HOUSING The most trusted jacks are now available in an in-line, cable end option. These jacks are designed for easy field installation and built to withstand challenging applications (not IP rated). Available in a variety of pin and bushing sizes, Switchcraft jacks are compatible with industry standard Switchcraft plugs.



TRUE FLEX RELIEF

Flexible rubber eliminates harsh bends and protects your cable from damage.
(see chart below)



CHUCK-STYLE STRAIN RELIEF

Easy to install, sturdy plastic strain relief protects critical solder connections.
(excludes ST10UC/ ST10UCF)



EXTENDED BUSHING FOR LOCKING PLUGS

Compatible with Switchcraft's locking plugs for an extremely reliable connection.
(also compatible with non-locking plugs)

SPECIFICATIONS

Lifecycles: 5,000 cycles min
Current: 5A or 11A (see list)
Cable range: 5.6mm to 6.4mm
(Without flex, max cable 8.1mm)
Split pin design for firm mate
Current carry only
See factory for overmolded cable options

PART NUMBER	PIN DIAMETER	BUSHING LENGTH	CURRENT RATING	FLEX RELIEF?	MATING PLUG
722ACF	2.0mm	5.5mm	5A	Yes	S760/ S760K
722AC	2.0mm	5.5mm	5A	No	S760/ S760K
712ACF	2.5mm	5.5mm	5A	Yes	760/ 760K
712AC	2.5mm	5.5mm	5A	No	760/ 760K
L722ACF	2.0mm	8.1mm	5A	Yes	S761/ S761K
L722AC	2.0mm	8.1mm	5A	No	S761/ S761K
L712ACF	2.5mm	8.1mm	5A	Yes	761/ 761K
L712AC	2.5mm	8.1mm	5A	No	761/ 761K
ST10UCF	1.9mm	8.3mm	11A	Yes	S10/ S10KS
ST10UC	1.9mm	8.3mm	11A	No	S10/ S10KS

VISIT WWW.SWITCHCRAFT.COM FOR DRAWINGS AND DETAILED SPECIFICATIONS