

How to Order

Part Number Explanation

Commercial Surface Mount Chips

EXAMPLE: 08055A101JAT2A

0805	5	A	101	J*	A	T	2	A
Size (L" x W")	Voltage	Dielectric	Capacitance	Tolerance	Failure Rate	Terminations	Packaging	Special Code
0201 0402 0603 0805 1206 1210 1812 1825 2220 2225	4 = 4V 6 = 6.3V Z = 10V Y = 16V 3 = 25V D = 35V 5 = 50V 1 = 100V 2 = 200V	A = NP0(C0G) C = X7R D = X5R G = Y5V U = U Series W = X6S Z = X7S	2 Sig. Fig + No. of Zeros Examples: 100 = 10 pF 101 = 100 pF 102 = 1000 pF 223 = 22000 pF 224 = 220000 pF 105 = 1µF 106 = 10µF 107 = 100µF For values below 10 pF, use "R" in place of Decimal point, e.g., 9.1 pF = 9R1.	B = ±.10 pF C = ±.25 pF D = ±.50 pF F = ±1% (≥ 25 pF) G = ±2% (≥ 13 pF) J = ±5% K = ±10% M = ±20% Z = +80%, -20% P = +100%, -0%	A = N/A	T = Plated Ni and Sn 7 = Gold Plated	<u>Available</u> 2 = 7" Reel 4 = 13" Reel 7 = Bulk Cass. 9 = Bulk	A = Std.
	Contact Factory for Special Voltages F = 63V 9 = 300V * = 75V X = 350V E = 150V 8 = 400V V = 250V					Contact Factory For 1 = Pd/Ag Term	Contact Factory For Multiples	
						* B, C & D tolerance for ≤10 pF values. Standard Tape and Reel material (Paper/Embossed) depends upon chip size and thickness. See individual part tables for tape material type for each capacitance value.		

High Voltage Surface Mount Chips

EXAMPLE: 1808AA271KA11A

1808	A	A	271	K	A	1	1A
AVX Style	Voltage	Temperature Coefficient	Capacitance Code	Capacitance Tolerance	Failure Rate	Termination	Packaging/Marking
1206 1210 1808 1812 1825 2220 2225 3640	7 = 500V C = 600V A = 1000V S = 1500V G = 2000V W = 2500V H = 3000V J = 4000V K = 5000V	A = C0G C = X7R	(2 significant digits + no. of zeros) Examples: 10 pF = 100 100 pF = 101 1,000 pF = 102 22,000 pF = 223 220,000 pF = 224 1 µF = 105	C0G: J = ±5% K = ±10% M = ±20% X7R: K = ±10% M = ±20% Z = +80%, -20%	A=Not Applicable	1 = Pd/Ag T = Plated Ni and Sn	1A = 7" Reel Unmarked 3A = 13" Reel Unmarked 9A = Bulk/Unmarked

Ultra Thin Surface Mount Chips

EXAMPLE: UT023C223MAT2A

UT	02	3	C	223	M	A	T	2	A
Style	Case Size	Voltage	Dielectric	Capacitance Code (In pF)	Capacitance Tolerance	Std.	Term	Packaging Code	Terminations Code (max.)
Ultrathin	01 = 0603 02 = 0805 03 = 1206	Y = 16Vdc 3 = 25Vdc 5 = 50Vdc	A = C0G C = X7R	2 Sig Digits + Number of Zeros			T = Plated Ni and Sn	2 = 7" reel	A = 0.50mm (0.020) B = 0.40mm (0.016) C = 0.35mm (0.014)

Please handle these products with due care as they are inherently more fragile than standard MLC capacitors because of their physical dimensions.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AVX:

[1812VC104MAT2A](#) [04025C471KAQ2A](#) [04025C821KAJ2A](#) [0402YC103JAJ2A](#) [0402YC103KAJ2A](#)
[0402YC153KAJ2A](#) [0402YC182JAJ2A](#) [0402YC472JAJ2A](#) [0402ZC333KAJ2A](#) [0402ZC393JAJ2A](#) [0201YC102JAQ2A](#)
[0201YC151KAQ2A](#) [04025C221KAQ2A](#) [04025C222JAQ2A](#) [06035C153KAJ4A](#) [1206AC101KAJ1A](#) [1206AC220KAJ1A](#)
[1206AC562MAJ1A](#) [1206CC102KAJ1A](#) [1206CC220KAJ1A](#) [1206GC220KAJ1A](#) [1812AC103MAQ1A](#)
[2220VC152KAT1A](#) [0201ZG103KAT2A](#) [06035C101JAJ2A](#) [06035C101KAJ2A](#) [06035C181KAJ2A](#) [06035C182KAJ2A](#)
[06035C271KAJ2A](#) [06035C272KAJ2A](#) [08055G104MAT2A](#) [12063G225MAT2A](#) [1812VC104KAT2A](#) [12065G104MAT2A](#)
[1206AC332KAJ1A](#) [3640CC564KAJ9A](#) [0201ZG103MAT2A](#) [3640SC853KAJ9A](#) [04025C102JAJ2A](#) [04025C122JAJ2A](#)
[04025C182JAJ2A](#) [04025C331JAJ2A](#) [04025C681JAJ2A](#) [06033C104KAJ2A](#) [06035C102KAJ2A](#) [18125C105KAJ4A](#)
[1206AC472KAJ1A](#) [1206CC103KAJ1A](#) [1206CC153KAJ1A](#) [1206CC472KAJ1A](#) [1206GC102KAJ1A](#) [3640CC474KAJ9A](#)
[1206GC152KAJ9A](#) [06035C104KAJ2A](#) [0805ZG475MAT2A](#) [1206YG225MAT2A](#) [1206AC102KAJ1A](#)
[06033G104MAT2A](#) [3640CC334KATBA](#) [1206AC100KAJ1A](#) [1206AC182KAJ1A](#) [1206AC472KAJ9A](#) [1812CC104KAJ9A](#)
[1825AC104KAJ9A](#) [1825AC333KAJ9A](#) [1825SC273KAJ9A](#) [1825SC333KAJ9A](#) [1206AC151KAJ1A](#)
[06035G183MAT2A](#) [1206VC104MAT2A](#) [1206VC103KAT2A](#) [0402YC103KAQ2A](#) [08055C104KAJ4A](#)
[0402YC102KAJ2A](#) [1206VC104KAT2A](#) [0603YC103KAJ2A](#) [04025C471KAJ2A](#) [1210VC104JAT2A](#) [1812VC394KAT2A](#)
[1825AC683KAJ1A](#) [1206DC105MAT2A](#) [18125C474KAJ2A](#) [1206VC473KAT2A](#) [18125C105KAJ2A](#)
[04025C152KAJ2A](#) [04023C103KAJ2A](#) [1206VC202JAT2A](#) [0805VC272JAT2A](#) [04023C222KAJ2A](#) [1206VC333KAT2A](#)
[1206VC101JAT2A](#) [1825GC562KAJ1A](#) [1206VC273KAT2A](#) [22258C224MAT1A](#) [0805VC561KAT2A](#) [1206DC104KAT2A](#)
[1206VC472KAT2A](#) [1206VC273JAT2A](#) [1206VC563KAT2A](#) [1210VC104KAT2A](#)