.100" × .100" for .050" Pitch Cable

D89 Series



- Preassembled, packaging on swords for easy loading of manual and semi-automatic assembly equipment
- · Bulk packaging option for maximum economy
- "Bumps" are designed to prevent premature latch locking during shipment
- Optional double-sided adhesive pull tab for easy
- unplugging
- Double-recessed cover for cable terminating from either side virtually eliminating the need for singlerecessed cover connectors
- Military polarization, with or without centerbump
- RoHS Compliant. See the Regulatory Information Appendix (RIA) in the "RoHS compliance" section of www.3Mconnectors.com for compliance information (RIA E1 & C1 apply)

Date Modified: August 21, 2013

TS-2243-G Sheet 1 of 3

Physical

Insulation:

Material: Glass Filled Polyester

Flammability: UL 94V-0

Color: Gray

Contact:

Material: Phosphor Bronze

Plating:

Underplating: 50μ " [1.27μ m] Nickel Wiping Area: 15μ " [0.38μ m] Gold

Wire Accommodation: 26 and 28 AWG Stranded

Marking: 3M Logo and Orientation Triangle

Electrical

Current Rating:	1 line	6 Adiacent Lines	All Lines

28 AWG 4.25 1.75 1.25 26 AWG 4.50 2.25 1.50

Rating Conditions: EIA-364-070 Method 2, 30°C maximum temperature rise, 20%

derated. Reference appropriate 3M Product Specification for detailed current

derating curves.


Insulation Resistance: $> 1 \times 10^9 \,\Omega$ at $500 \, V_{DC}$ Withstanding Voltage: $1{,}000 \, V_{RMS}$ at Sea Level

Environmental


Temperature Rating: -55°C to +105°C

UL File No.: E68080

3M



.100" × .100" for .050" Pitch Cable



Important Notice All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M. Warranty; Limited Remedy; Limited Liability. This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the

warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of

the legal theory asserted.

6801 River Place Blvd. Austin, TX 78726-9000

www.3Mconnectors.com

U.S.A. 1-800-225-5373

3M Electronics Solutions Division

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

D89144-0031HK D89144-0101HK D89116-0131HK D89126-0131HK D89160-0131HK D89124-0131HK D89136-0131HK D89110-0101HK D89124-0101HK D89130-0101HK D89134-0101HK D89160-0101HK D89110-0031HK D89116-0031HK D89124-0031HK D89126-0031HK D89136-0031HK D89140-0031HK D89150-0031HK D89160-0031HK D89124-0001HK D89126-0001HK D89130-0001HK D89136-0001HK D89140-0001HK D89150-0001HK D89160-0001HK D89160-0001HK D3448-89110 D3448-89130