

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Cordless Jigsaw

GST 18 V-LI S



Powerful barrel grip jigsaw in the 18 V category

The most important data

Battery voltage	18 V
Cutting depth in wood	120 mm
Cutting depth in aluminium	20 mm

Part Number 0 601 5A5 100[> More product information](#)

Technical data

Technical data

Stroke rate at no load	550 – 2,700 spm
Stroke height	23 mm
Weight excl. battery	1.8 kg
Battery voltage	18 V
Packaging dimensions (width x length x height)	335 x 420 x 123 mm
Weight incl. battery	2.4 kg

'Total vibration values (Sawing wood)'

Vibration emission value ah	7.5 m/s ²
Uncertainty K	1.5 m/s ²

'Total vibration values (Sawing sheet metal)'

Vibration emission value ah	8 m/s ²
Uncertainty K	1.5 m/s ²

Cutting depth

Cutting depth in wood	120 mm
Cutting depth in aluminium	20 mm
Cutting depth in unalloyed steel	8 mm

Noise/vibration information

Sawing wood

Vibration emission value ah	7.5 m/s ²
Uncertainty K	1.5 m/s ²

Sawing sheet metal

Vibration emission value ah	8 m/s ²
Uncertainty K	1.5 m/s ²



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Narrow barrel grip provides optimal control even when cutting from underneath
- Tool-free Bosch SDS-system makes changing saw blades easy
- Strong 18 V performance enables fast work progress

