



Connector Location A

Connector Location B





Loading-Plan

X female



- 1 brown 1
- 2 blue 2
- 3 white 3
- 4 green 4
- 5 pink 5
- 6 yellow 6
- 7 black 7
- 8 grey 8
- 9 red 9
- 10 violet 10
- 11 grey-pink 11
- 12 red-blue 12

Y male



length in "1m" step	100	XXX=000
	99	XXX=990

length in "0.1m" step	12	XXX=120
	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098

Step	a [m]	XXX

4.0 to 100	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

PUR black, 12x0.14mm ²	21348485C78XXX
Type of cable	Part no.

- Protection level: IP67
- Temperature range: -30°C ... +80°C

	All Dimensions in mm	Tech. Character.	Free size tol.	According to production drawing
	All rights reserved Department HCS - RO	Created by STOCHECIC Stocheici	Inspected by COSTEA Costea	Standardisation MUNTEANV Muntean
HARTING Customised Solutions D-32339 Espelkamp		Title M12 Cable Assembly A-cod st/st f/m		Date 2019-01-14
		Type TB	Number 21348485C78XXX	State Final Release
				Doc-Key / ECM-Nr. 100808603/UGD/009/A 500000144928
				Rev. A Page 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[21348485C78015](#) [21348485C78075](#) [21348485C78100](#) [21348485C78005](#) [21348485C78010](#) [21348485C78020](#)
[21348485C78050](#)