

Barrier & Dead Front Terminal Blocks

Series 14002 & 14004

Barrier Terminal Blocks

Inches (Millimeters)

Series 14002

SPECIFICATIONS

Ratings: 115A, 600V; UL/CSA

Poles: 2 to 6 poles

Wire sizes: #2 – #14 CU/#8 AL

Operating temperature: 150°C

Marking: Marking strip optional, consult factory.

Options: CP = Pressure plate, rated 60A, 600V

Q = Quick-Connect, rated 50A, 600V

To order options, enter letter code


in front of Part No.: ie; CP14002-2

Agency approvals: UL E62622; CSA LR15364;

CE Pending



14002-2



Part Number	A	B
14002-2	1.75	–
14002-3	2.37	–
14002-4	3.34	1.59
14002-5	3.96	2.21
14002-6	4.59	2.84

Note: "A" dimension for 14002-2 & 14002-3 only.
(14002-2 & 14002-3 have only two mounting holes.)

Dead Front Terminal Blocks

Inches (Millimeters)

Series 14004

SPECIFICATIONS

Ratings: 90A, 600V; UL/CSA

Poles: 2 to 12 poles

Wire sizes: #4 – #14 CU/#8AL


Operating temperature: 75°C

Marking: Marking strip optional, consult factory.

Agency approvals: UL E62622; CSA LR15364



14004-4



Part Number	A	B
14004-2	1.81	1.43
14004-3	2.31	1.93
14004-4	2.81	2.43
14004-5	3.31	2.93
14004-6	3.81	3.43
14004-7	4.31	3.93
14004-8	4.81	4.93
14004-9	5.31	4.93
14004-10	5.81	5.43
14004-11	6.31	5.93
14004-12	6.81	6.43

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[14004-12](#) [14004-11](#) [14004-10](#) [14004-8](#) [14004-2](#) [14004-6](#) [14004-4](#) [14004-9](#) [14004-7](#) [14004-5](#) [14004-3](#) [14002-2](#)
[14002-5](#) [14002-4](#) [14002-3](#) [14002-3A](#) [Q14002-3](#) [CP14002-4](#) [14002-2A](#) [14004-12A](#)