




PLT.6SM  
PLT.7M  
HEAD VIEW



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT.6SM	.01 (.3)	.6 (15)	.030 (.76)	.070 (1.8)	.124 (3.1)	.095 (2.4)	.125 (3.2)	2.8 (71)	8 (36)	SUB-MINIATURE	CURVED	.02 (9.0)
PLT.7M	.03 (.8)	.68 (17)	.032 (.8)	.090 (2.3)	.148 (3.8)	.115 (2.9)	.180 (4.6)	3.1 (79)	18 (80)	MINIATURE	CURVED	.04 (16)
PLT1M	.06 (1.5)	.87 (22)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	3.9 (99)	18 (80)	MINIATURE	CURVED	.07 (32)
PLT1.5M	.06 (1.5)	1.25 (32)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	5.6 (142)	18 (80)	MINIATURE	CURVED	.10 (45)
PLT2M	.06 (1.5)	2.00 (51)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	8.0 (203)	18 (80)	MINIATURE	CURVED	.13 (59)
PLT1.5I	.06 (1.5)	1.38 (35)	.045 (1.1)	.142 (3.6)	.206 (5.2)	.180 (4.6)	.240 (6.1)	5.6 (142)	40 (178)	INTERMEDIATE	CURVED	.14 (64)
PLT2I	.06 (1.5)	2.00 (51)	.045 (1.1)	.142 (3.6)	.206 (5.2)	.180 (4.6)	.240 (6.1)	8.0 (203)	40 (178)	INTERMEDIATE	CURVED	.20 (91)
PLT2.5I	.06 (1.5)	2.50 (64)	.052 (1.3)	.145 (3.7)	.220 (5.6)	.180 (4.6)	.260 (6.6)	9.7 (246)	40 (178)	INTERMEDIATE	CURVED	.27 (122)

NOTES:

\*SEE [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							PAN-TY CABLE TIE - PLT SERIES	CEW	12-27-84	HVP	NONE		A
							CUSTOMER DRAWING						
							ITEM REVISION NAME						
							W10001CA/34						
							DATASET FILE NAME						
							W10001CA/34-SS-5540 SH1_REV34						
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)						
							.x ± --- .xxx ± .020 (.51)						
							.xx ± .02 (.5) ANGLES ± ---						
							THIRD ANGLE PROJECTION						
							MATERIAL:						
							NYLON 6.6						
							DRAWING NUMBER:						
							SS-5540 SHEET 1						

D10100DA/16

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Panduit:

[PLT2M-M30](#) [PLT1M-M8](#) [PLT1M-M0](#) [PLT1M-C0](#) [PLT.6SM-M0](#) [PLT1M-M](#) [PLT2I-M](#) [PLT2I-M2](#) [PLT2M-M0](#)  
[PLT2.5I-C](#) [PLT.6SM-C](#) [PLT2.5I-M](#) [PLT2.5I-M0](#) [PLT.6SM-M30](#) [PLT1.5I-C0](#) [PLT1.5I-C20](#) [PLT1.5I-C30](#) [PLT1.5I-M00](#)  
[PLT1.5M-C](#) [PLT1.5M-C0](#) [PLT1.5M-M30](#) [PLT1.5M-M5](#) [PLT1.5M-M8](#) [PLT1M-C00](#) [PLT1M-C4Y](#) [PLT1M-C8](#) [PLT1M-](#)  
[MP0](#) [PLT1M-M1](#) [PLT1M-M10](#) [PLT1M-M2](#) [PLT1M-M20](#) [PLT1M-M4Y](#) [PLT1M-M5](#) [PLT1M-M6](#) [PLT2I-C30](#) [PLT2I-](#)  
[M30](#) [PLT2M-M20](#) [PLT1.5I-C7](#) [PLT2I-M20](#) [PLT1.5I-M6](#) [PLT1.5I-C4Y](#) [PLT1M-C7](#) [PLT1M-M14](#) [PLT1.5I-C10](#) [PLT2I-](#)  
[M8](#) [PLT1.5M-M6](#) [PLT1.5I-M7](#) [PLT1.5I-C5](#) [PLT2I-M7](#) [PLT2I-M6](#) [PLT2I-M10](#) [PLT2I-C14](#) [PLT2M-M5](#) [PLT1M-C14](#)  
[PLT1.5I-C1](#) [PLT1.5I-C8](#)