



SPECIFICATIONS - ERG50

1. INSTALLS 18-50 LB (80-222 N) CABLE TIES
2. ADJUSTABLE TENSION SETTINGS 1-8
3. INTEGRATED TENSION LOCKING SCREW
4. 360° ROTATING NOSE
5. ANTI-RECOIL MECHANISM
6. ADJUSTABLE GRIP SPAN
7. SELECTABLE MODE HIGH-LOW HANDLE FORCE
8. 1" [25.4mm] STROKE IN HIGH, 0.5" [12.7mm] STROKE IN LOW
9. HIGH IMPACT POLYMER CONSTRUCTION WITH SOFT OVERMOLDED GRIP
10. SPARE BLADE STORAGE - SPARE BLADE PART# - CDS010461

GENERAL NOTES		THIRD ANGLE PROJECTION		 www.tnb.com			
1. ALL DIMENSIONS ARE FOR REFERENCE ONLY. 2. DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.							
REVISIONS		DESCRIPTION:		ERG50 Ty-RAP INSTALLATION TOOL			
- SEE ERN (****) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: ****		ORIGINAL PROJECT NO / (ERN NO)	SHEET NO:	REV. NO:	DRAWING NO:		
		FD55446 / (2008035)	1 OF 1	-	WSD000333		