

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	15[mm]
Max. Air Flow:	18.4[CFM]
Max. Air Flow:	0.52[m ³ per min]
Max. Static Pressure:	0.21[In H ₂ O]
Max. Static Pressure:	51.2[Pa]
Fan Speed:	4600[RPM]
Noise:	34[dB]
Life Expectancy:	25 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	10[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.1[A]
Input Power:	2.4[W]
Mass:	45[g]
Tach / Locked Rotor Output:	No
Status:	Active