



preci-dip

SPRING-LOADED CONNECTORS & PAD CONNECTORS

SERIES
811

811-S1-NNN-10-XXX101
Single Row
2.54 mm, Straight solder tail

Low resistance modular connectors with spring-loaded contacts (SLC), solder tail. Contacts with improved, shaped piston design.



TECHNICAL SPECS.:

Flammability	UL 94V-O
Piston and barrel	Brass CuZn36Pb3 (C36000)
Contact clip	Beryllium copper (C17200)
Spring	Music wire DIN 17223, gold plated
Max. stroke	1.4 mm
Forces initial	0.25 N
Forces initial at 1/2 stroke	0.85 N
Mechanical life	50'000 cycles
Max. operating current	3.5 A
Contact resistance	10 m (static measurement, halfway position)
Plating	Barrel: 0.25 µm gold - Piston: 0.5 µm gold

ORDERING INFORMATION:

Initial height A (mm)	Height plastic body B (mm)	XXX code
6	4	014
6.5	4	015
7	4	016
7.5	4	017

NNN number of poles. Replace NNN with the requested number of poles, e.g. 811-S1-NNN-10-014101 for a single row version with 16 pins becomes 811-S1-016-10-014101.

TECHNICAL ASSISTANCE

GENERAL SPECIFICATIONS:

The values listed below are general specs applying for PRECI-DIP spring-loaded connectors. Please see individual catalog page for additional and product specific technical data.

Operating temperature range	-55 ... +125 °C
Climatic category (IEC)	55/85/21
Operating humidity range	annual mean 75 %
Max working voltage	100 VRMS/150 VDC (2.54 mm grid)

PRECI-DIP products are recognized by Underwriters Laboratories Inc. and listed under "Connectors for Use in Data, Signal, Control and Power Applications", File Nr. E174442.

ELECTRICAL CHARACTERISTICS:

Insulation resistance between any two adjacent contacts	Min. 10'000 M at 500 V AC
Capacitance between any two adjacent contacts	Max. 1 pF

ENVIRONMENTAL CHARACTERISTICS:

The sockets withstand the following environmental tests without mechanical and electrical defects:

- Dry heat steady state IEC 60512-11-9.11i / 60068-2-2.Bb: 125 °C, 16h
- Damp heat cyclic IEC 60512-11-12.11m / 60068-2-30.Db: 25/55 °C, 90 – 100 %rH, 1 cycle of 24 h
- Cold steady state IEC 60512-11-10.11j / 60068-2-1.A: -55 °C, 2 h
- Thermal shock IEC 60512-11-4.11d / 60068-2-14.Na: -55/125 °C, 5 cycles 30 min
- Sinusoidal vibrations IEC 60512-6-4.6d / 60068-2-6.Fc: 10 to 500 Hz, 10 g, 1 octave/min, 10 cycles for each axis
- Shock IEC 60512-6-3.6c / 60068-2-27.Ea: 50 g, 11 ms, 3 shocks in three axis

During the above two tests no contact interruption >50 ns does appear.

- Solderability J-STD-002A, Test A, 245°C, 5 s solder alloy SnAg3.8Cu0.7
- Resistance to soldering heat J-STD-0020C, 260°C, 20 s
- Moisture sensitivity J-STD-020C level 1
- Resistance to corrosion :
 - 1) Salt spray test IEC 60068-2-11.Ka: 48 h
 - 2) Sulfur dioxide (SO₂) test IEC 60068-2-42 Kc: 96 h at 25 ppm SO₂, 25 °C, 75 %rH
 - 3) Hydrogen sulfide (H₂S) test IEC 60068-2-43 Kd: 96 h at 12 ppm H₂S, 25 °C, 75 %rH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Preci-dip:

[811-S1-021-10-016101](#) [811-S1-011-10-014101](#) [811-S1-022-10-014101](#) [811-S1-021-10-014101](#) [811-S1-020-10-014101](#) [811-S1-019-10-014101](#) [811-S1-064-10-017101](#) [811-S1-063-10-017101](#) [811-S1-062-10-017101](#) [811-S1-061-10-017101](#) [811-S1-060-10-017101](#) [811-S1-059-10-017101](#) [811-S1-051-10-016101](#) [811-S1-050-10-016101](#) [811-S1-049-10-016101](#) [811-S1-048-10-016101](#) [811-S1-060-10-016101](#) [811-S1-056-10-017101](#) [811-S1-057-10-016101](#) [811-S1-056-10-016101](#) [811-S1-055-10-016101](#) [811-S1-054-10-016101](#) [811-S1-053-10-016101](#) [811-S1-052-10-016101](#) [811-S1-063-10-016101](#) [811-S1-062-10-016101](#) [811-S1-061-10-016101](#) [811-S1-045-10-016101](#) [811-S1-059-10-016101](#) [811-S1-008-10-017101](#) [811-S1-005-10-017101](#) [811-S1-004-10-017101](#) [811-S1-003-10-017101](#) [811-S1-002-10-017101](#) [811-S1-064-10-016101](#) [811-S1-025-10-016101](#) [811-S1-024-10-016101](#) [811-S1-023-10-016101](#) [811-S1-035-10-016101](#) [811-S1-058-10-016101](#) [811-S1-058-10-017101](#) [811-S1-031-10-016101](#) [811-S1-030-10-016101](#) [811-S1-029-10-016101](#) [811-S1-028-10-016101](#) [811-S1-027-10-016101](#) [811-S1-026-10-016101](#) [811-S1-037-10-016101](#) [811-S1-036-10-016101](#) [811-S1-046-10-016101](#) [811-S1-034-10-016101](#) [811-S1-047-10-016101](#) [811-S1-032-10-016101](#) [811-S1-043-10-016101](#) [811-S1-042-10-016101](#) [811-S1-041-10-016101](#) [811-S1-040-10-016101](#) [811-S1-039-10-016101](#) [811-S1-038-10-016101](#) [811-S1-035-10-017101](#) [811-S1-007-10-017101](#) [811-S1-046-10-017101](#) [811-S1-033-10-016101](#) [811-S1-009-10-017101](#) [811-S1-044-10-016101](#) [811-S1-041-10-017101](#) [811-S1-040-10-017101](#) [811-S1-039-10-017101](#) [811-S1-038-10-017101](#) [811-S1-037-10-017101](#) [811-S1-036-10-017101](#) [811-S1-047-10-017101](#) [811-S1-032-10-017101](#) [811-S1-045-10-017101](#) [811-S1-033-10-017101](#) [811-S1-043-10-017101](#) [811-S1-042-10-017101](#) [811-S1-053-10-017101](#) [811-S1-052-10-017101](#) [811-S1-051-10-017101](#) [811-S1-050-10-017101](#) [811-S1-049-10-017101](#) [811-S1-048-10-017101](#) [811-S1-011-10-017101](#) [811-S1-010-10-017101](#) [811-S1-022-10-017101](#) [811-S1-044-10-017101](#) [811-S1-055-10-017101](#) [811-S1-054-10-017101](#) [811-S1-017-10-017101](#) [811-S1-016-10-017101](#) [811-S1-015-10-017101](#) [811-S1-014-10-017101](#) [811-S1-013-10-017101](#) [811-S1-012-10-017101](#) [811-S1-023-10-017101](#) [811-S1-057-10-017101](#) [811-S1-021-10-017101](#) [811-S1-034-10-017101](#) [811-S1-019-10-017101](#)