



Quality Products. Service Excellence.

Heavy Duty Outlet Strip 1581 Series

10A | 100-240V | C13 Outlets



Features

- Rated 100-240VAC (TUV), 120-240VAC (UL), 10 A, 50/60 Hz and designed for use with IEC power cords
- All metal housing – tough extruded aluminum case with black powder-coated steel cover.
- On-Off switch is rocker type with green light (on those units with on-off switch - listed below) or a green pilot light to indicate power on.
- Mounting feet (with keyhole slots) allow temporary work station mounting if desired.

Specifications

- One IEC 320 - C14 inlet, and 4, 5, 6 or 8 IEC 320 - C13 outlets.
- Includes 10A circuit breaker to prevent accidental line overload.
- cULus Listed UL 62368-1 (2nd Edition), 2014-12-01, and CAN/CSA C22.2 No. 62368-1-14 (2nd Edition)
- TÜV-SUD Certified to EN 62368-1:2014/A11:2017, and IEC 62368-1:2014 (2nd Edition)
- TÜV-SUD tested for EMC Compliance to EN 55032:2012 (CISPR 32:2012) & EN 55024:2010 (CISPR 24:2010).
- CE compliant to the European Low Voltage Directive 2014/35/EU.
- CE compliant to the European EMC Directive 2014/30/EU.

Accessories

- Rack Cabinet Vertical Mount Adaptor
- Input Accessory Cords



Illuminated On/Off Switch	Illuminated Light Only	Overall Dimensions			Outlet Qty	Outlet Type	Inlet Type
		Height	Width	Length			
Part No.	Part No.						
1581H4	1581T4	2.33	2.13	10.18	4	C13	C14
1581H5	1581T5	2.33	2.13	11.75	5	C13	C14
1581H6	1581T6	2.33	2.13	13.36	6	C13	C14
1581H8	1581T8	2.33	2.13	16.51	8	C13	C14

Replacement Mounting Foot (One Foot)

Part No.	1584MF
----------	--------

Data subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[1581T6](#) [1581T4](#) [1581T5](#) [1581T8](#) [1581H8](#) [1581H5](#) [1581H6](#) [1581H4](#)