




TAH80

80 Series Adjustable Wrenches with Quick Link



PRODUCT DETAILS


- Non-reversible jaw
- Head combines slim design
- Handle type 80 series
- High-performance alloy steel forged in one single piece
- Chrome or phosphate finish options
- Standards: ISO 6787, DIN 3117, ASME B107.8M - 1996 and BS 6333
- Suitable for working at height
- Permanently fixed stainless steel quick link, maintains user ergonomics and full functionality
- Colour plate with maximum weight to match with lanyard
- According to DROPS best practices



Follow the Fish!



PRODUCT ATTRIBUTES

| Product | A | A | B | C | D | E |  g |
|-----------------|----------|----------|----------|----------|----------|----------|---|
| TAH8069 | 110 mm | 4 in | 13 mm | 4 mm | 9 mm | 13 mm | 77 g |
| TAH8070 | 155 mm | 6 in | 20 mm | 5,3 mm | 11,5 mm | 19 mm | 148 g |
| TAH8071 | 205 mm | 8 in | 27 mm | 6 mm | 13 mm | 24 mm | 267 g |
| TAH8072 | 255 mm | 10 in | 31 mm | 8,6 mm | 15,5 mm | 29 mm | 442 g |
| TAH8073 | 305 mm | 12 in | 34 mm | 11,9 mm | 18 mm | 34 mm | 655 g |
| TAH8074 | 380 mm | 15 in | 44 mm | 13 mm | 21,5 mm | 44 mm | 1200 g |
| TAH8075 | 460 mm | 18 in | 53 mm | 17,7 mm | 22,5 mm | 53 mm | 1856 g |
| TAH8069C | 110 mm | 4 in | 13 mm | 4 mm | 9 mm | 13 mm | 80 g |
| TAH8070C | 155 mm | 6 in | 20 mm | 5,3 mm | 11,5 mm | 19 mm | 145 g |
| TAH8071C | 205 mm | 8 in | 27 mm | 6 mm | 13 mm | 24 mm | 269 g |
| TAH8072C | 255 mm | 10 in | 31 mm | 8,6 mm | 15,5 mm | 29 mm | 451 g |
| TAH8073C | 305 mm | 12 in | 34 mm | 11,9 mm | 18 mm | 34 mm | 728 g |
| TAH8074C | 380 mm | 15 in | 44 mm | 13 mm | 21,5 mm | 44 mm | 1177 g |
| TAH8075C | 455 mm | 18 in | 53 mm | 17,7 mm | 22,5 mm | 53 mm | 1804 g |

