



Click [here](#) for the 3D model.

Dimensions

D	18mm MAX
T	17mm MAX
H	20mm MAX
LL	5mm +/-2mm
S	8mm NOM
S1	13mm NOM
Wire Size	0.85mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	300
Typical Component Weight	6.5 g

General Information

Series	SC-GJ
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	0.36 mH
Current	7 A
Temperature Range	-40/+120°C
DC Resistance	14 mOhms