



### MATERIALS:

#### Body and Fittings:

- Shell - Brass, Tarnish Resistant Plating
- Center Contact - Gold Plated Phosphor Bronze
- Dielectric - PTFE

### RATING:

Operating Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 500VRMS Max.

Operating Temperature: -55°C to +85°C (-67°F) (+185°F)

Nominal Impedance: Non-Constant Impedance.

### ORDERING INFORMATION: Model 3287

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02$ " (.51 mm), .xxx =  $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[3287](#)