

Coaxial Cable Connector 11_MMCX-50-2-3/111_O

Description

Straight cable plug

Interface standards
SUHNER-MMCX



Technical Data

Electrical Data

| | |
|--------------------------|-------|
| Impedance | 50 Ω |
| Interface frequency max. | 6 GHz |

Mechanical Data

| | |
|----------------|-----------|
| Centre contact | crimped |
| Outer contact | crimped |
| Weight | 0.0008 kg |

Environmental Data

| | |
|--|------------------|
| Operating temperature | -55 °C to 155 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|------------------------|--|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact | Brass | Gold Plating (without Nickel underplating) |
| Body | Brass | Gold Plating (without Nickel underplating) |
| Insulator | PFA / PTFE | |
| Crimp ferrule | Copper | Gold Plating (without Nickel underplating) |

Related Documents

| | |
|----------------------|----------------|
| Outline drawing | DOU-00006967 |
| Catalogue drawing | DOU-00006969 |
| Assembly instruction | DOC-0000180916 |

Ordering Information

| | |
|----------------------|-----------------------|
| Single package | 11_MMCX-50-2-3/111_OE |
| Bulk 100 pcs package | 11_MMCX-50-2-3/111_OH |

Additional Information

| | |
|-----------------|--|
| Suitable cables | ENVIROFLEX_316, RG_316_U, RG_188_A/U, RG_174_U |
|-----------------|--|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11_MMCX-50-2-3/111_OH](#)