

## Plug SLS425-SE...


Stackable, Ø 4 mm, with spring-loaded MULTILAM, for self-assembly of test leads. With rigid insulating sleeve. Nickel-plated and gold-plated versions available.


## Various types of connection:

SLS425-SE/M: Screw connection SLS425-SE(/N): Cylindrical soldering surface SLS425-SE/Q(/N): Cross hole for solder

connection







Order No.	Туре	Rated voltage/current	Cable (A)			*Standard colors
22.2656-*	SLS425-SE/M	1000 V, CAT II / 32 A 600 V, CAT III / 32 A	~ Ø 3.9 mm	0.75 2.5 mm²	Au	20 21 22 23 24   25 26 27 28 29
22.2655-*	SLS425-SE	1000 V, CAT II / 32 A 600 V, CAT III / 32 A	~ Ø 3.9 mm	0.75 2.5 mm²	Au	20 21 22 23 24   25 26 27 28 29
22.2654-*	SLS425-SE/N	1000 V, CAT II / 32 A 600 V, CAT III / 32 A	~ Ø 3.9 mm	0.75 2.5 mm²	Ni	20 21 22 23 24   25 26 27 28 29
22.2658-*	SLS425-SE/Q	1000 V, CAT II / 32 A 600 V, CAT III / 32 A	~ Ø 3.9 mm	0.75 2.5 mm²	Au	20 21 22 23 24   25 26 27 28 29
22.2657-*	SLS425-SE/Q/N	1000 V, CAT II / 32 A 600 V, CAT III / 32 A	~ Ø 3.9 mm	0.75 2.5 mm²	Ni	20 21 22 23 24 25 26 27 28 29

## Component parts

22.2380-*	KT425-SE	Insulator (*Colors see: SLS425-SE/M)
22.1027	LS425-SE/M	Plug suitable for: SLS425-SE/M
22.1047	LS425-SE	Plug suitable for: SLS425-SE
22.1048	LS425-SE/N	Plug suitable for: SLS425-SE/N
22.1203	LS425-SE/Q	Plug suitable for: SLS425-SE/Q
22.1204	LS425-SE/Q/N	Plug suitable for: SLS425-SE/Q/N



## Assembly instructions MA161

www.staubli.com/electrical