

# FLOJET

a xylem brand

## G575215A

*Air Operated Diaphragm Pump*

- ◆ Capable of Air or CO<sub>2</sub> drive pressures up to 100PSI (6.9bar)
- ◆ Run dry capability, temperature range up to 49°C (120°F)
- ◆ Patented Shuttle Valve, eliminates stalling
- ◆ Capable of passing solids up to 3.2mm diameter.
- ◆ Corrosion resistant materials capable of handling a wide range of chemicals
- ◆ Other elastomers available
- ◆ Large exhaust silencer
- ◆ Ease of Installation with all quick disconnect ports
- ◆ Other port sizes available

Mounted in working position




**CONNECTIONS:** Product inlet and outlet 12.7mm (½" hose). Gas inlet 6mm (¼" hose)

**MATERIALS OF CONSTRUCTION:**

Pump head: Glass-filled Polypropylene  
 Diaphragm: Santoprene®  
 Valves: Santoprene® Check valves with Hastelloy springs  
 Seal Rings EPDM

**OUTPUT:**

Self primes up to 4.5m  
 Flow rates up to 21 litres/minute (4.6 gallons/minute).



**WEIGHT:** 0.7 Kg

