


IP68 SEALED USB PANEL MOUNT

Mates with:

RCU (Single Port only)

SPECIFICATIONS

For complete specifications see www.samtec.com?RPBU

Insulator Material:

Black Liquid Crystal Polymer

Contact:

Phosphor Bronze

Current Rating:

4.2 A per pin

(1 pin powered)

Operating Temp Range:

-20 °C to +80 °C

Seal: Silicone

Lead-Free Solderable:

Yes

DUST CAPS

- DCA-RPBU-01-01-A
- DCA-RPBU-02-01-A
- DCA-RPBU-01-01-B

RPBU	NO. OF PORTS	PLATING	TYPE	LEAD STYLE	OPTION												
	-01 = Single Port -02 = Dual Port (-A only)	-S = 30 μ" (0.76 μm) Gold on contact, Matte tin on tail	-A = USB A Type -B = USB B Type	-VT = Vertical Through-hole -RA = Right-angle	-LC = Locking Clip (-VT only)												
TYPE -B -B-VT -B-RA TYPE -A -A-VT -A-RA <table><tr><th>NO. OF PORTS</th><th>A</th><th>B</th><th>C</th></tr><tr><td>-01</td><td>(48.15) 1.896</td><td>(39.10) 1.539</td><td>(20.01) .788</td></tr><tr><td>-02</td><td>(69.80) 2.748</td><td>(60.75) 2.392</td><td>(42.00) 1.654</td></tr></table>						NO. OF PORTS	A	B	C	-01	(48.15) 1.896	(39.10) 1.539	(20.01) .788	-02	(69.80) 2.748	(60.75) 2.392	(42.00) 1.654
NO. OF PORTS	A	B	C														
-01	(48.15) 1.896	(39.10) 1.539	(20.01) .788														
-02	(69.80) 2.748	(60.75) 2.392	(42.00) 1.654														

Mates with:

RPCU

SPECIFICATIONS

For complete specifications see www.samtec.com?RPCU

Insulator Material:

Black Liquid Crystal Polymer

Contact Material:

Phosphor Bronze

Operating Temp Range:

-20 °C to +80 °C

Shield Material:

Phosphor Bronze

Wire:

20 AWG (Power)

25 AWG (Signal)

28 AWG (Drain)

DUST CAPS

- DCA-RPBU-01-01-A
- DCA-RPBU-01-01-B

RPCU	PLATING	CABLE LENGTH	END 1 OPTION	END 2 OPTION
	-G = 30 μ" (0.76 μm) Gold on contact, Nickel on shell	-00.25 = (0.25 m) 9.84" Cable -00.50 = (0.50 m) 19.68" Cable Standard lengths (Assembled Length = Cable Length + (42.8 mm) 1.69")	-AMS = USB A Type, Sealed -BMS = USB B Type, Sealed	-AM = USB A Type, Not Sealed -BM = USB B Type, Not Sealed -BC = Blunt Cut
		ALSO AVAILABLE (MOQ Required) • Other wire lengths		

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[RPBU-01-S-A-VT](#) [RPBU-01-S-B-RA](#) [RPBU-01-S-A-VT-LC](#) [RPBU-01-S-A-RA](#) [RPBU-02-S-A-VT](#) [RPBU-02-S-A-VT-LC](#) [RPBU-01-S-B-VT](#) [RPBU-01-S-B-VT-LC](#) [RPBU-02-S-A-RA](#) [DCA-RPBU-02-01-A](#)