



PART NO.	SHEET THICKNESS (REF.)	"A" +.015 -.005	"B" +.015 -.005	"C" +.015 -.005	"D" +.020 -.005
MGS-1-01	.015-.052 (0.4-1.3)	.150 (3.8)	.056 (1.4)		
MGS-2-01	.052-.085 (1.3-2.2)	.175 (4.4)	.090 (2.3)	.055 (1.4)	.100 (2.5)
MGS-3-01	.085-.128 (2.2-3.3)	.220 (5.6)	.131 (3.3)		
MGS-4-01	.128-.192 (3.3-4.9)	.325 (8.3)	.195 (5.0)	.070 (1.8)	.160 (4.1)
MGS-5-01	.192-.255 (4.9-6.5)	.385 (9.8)	.260 (6.6)	.070 (1.8)	.170 (4.3)
MGS-6-01	.255-.318 (6.5-8.1)	.445 (11.3)	.320 (8.1)	.075 (1.9)	.180 (4.6)

NOTES:

1. MATERIAL: NYLON 66 (RMS-01).
2. COLOR: NATURAL.

B	UPDATED PRINT	SM 03.12.02
A	CHANGED FILE NO. AND TITLE BLOCK	SM 06.19.01
REV	DESCRIPTION	ENGR DATE

TITLE: MOLDED GROMMET STRIP				DWG IN IN (MM)		FINAL	
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°		FILE # MGS	DWN: P.B.	APP:	PART #		
		MAT'L: SEE NOTES	DT: 05-02-94	DT:	SEE TABLE		
		RE: RICHCO, INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060		PRINT TYPE CA		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[MGS-3-01](#) [MGS-5-01](#) [MGS-1-01](#) [MGS-2-01](#) [MGS-4-01](#) [MGS-6-01](#) [MGS-8-01](#)