

Notes:

- 1) This is not an isolating transformer
- 2) **There is no earth connection**
- 3) Do not operate at maximum load for more than 1 hour
- 4) Single shot thermal fuse protected.


Specification (@ 240V, 50Hz):

Input voltage range: 220V - 240VAC
 Input frequency: 50Hz
 Magnetising current: 90mA (typical)

Off load output voltage: 121V
 Output voltage: 114VAC, 50Hz @ 375mA
 Regulation: 5.8%
 Maximum output power: 45VA
 Output socket: polarised NEMA 1 - 15R

Mass: 0.45kg

Tolerance on all dimensions unless stated otherwise: +/- 1mm



Walters Group Holdings Ltd.
 Unit 5, Oxonian Park, Langford Locks,
 Kidlington, Oxfordshire. OX5 1FP
 Tel: (01865) 855085 Fax: (01865) 855075
 Website: www.oep.co.uk

DESCRIPTION	ISSUE	DATE	DRAWN	CHECKED	DRAWING NUMBER
Enclosure dimensions of MW2P045-E	1	27/09/13	CS		MW2P045-E
Scale: nts	All dimensions in mm unless stated otherwise				