

## Han 3EMC-HBM-SL



Image is for illustration purposes only. Please refer to product description.

Part number	09 62 003 0301
Specification	Han 3EMC-HBM-SL
HARTING eCatalogue	<a href="https://b2b.harting.com/09620030301">https://b2b.harting.com/09620030301</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> EMC
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Straight

### Version

Size	3 A
Locking type	Single locking lever
Field of application	Hoods/Housings for higher EMC requirements

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	12

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	PTFE
Material (locking)	Steel



Pushing Performance  
Since 1945

## Material properties

Surface (locking)	Zinc plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	564b7d75-7bf6-4cfb-acb1-2168eb61b675
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

CE	Yes
Approvals	DNV GL

## Commercial data

Packaging size	10
Net weight	35 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140073005
eCl@ss	27440202 Shell for industrial connectors