



Click [here](#) for the 3D model.

Dimensions

Chip Size	1210
L	3.2mm +/-0.3mm
W	2.5mm +/-0.25mm
T	1.3mm
B	0.5mm +/-0.25mm

Packaging Specifications

Packaging	T&R
Packaging Quantity	2500

General Information

Series	VA
Type	Varistors
Style	SMD Chip
Description	SMD 125C Multilayer Chip Varistor, 12V Power Supply
Features	Automotive
Termination	Nickel Tin
RoHS	Yes
Qualifications	IEC, AEC-Q200
AEC-Q200	Yes

Specifications

Voltage DC	16 VDC (25C)
Voltage AC	14 VAC
Temperature Range	-55/+125°C
Storage Temperature Range	-55/+150°C
Varistor Voltage	24 VDC at 1 mA
Jump Start Voltage	24.5 VDC (5 min)
Clamping Voltage	40 V
Clamping Current	2.5 A (8/20 us MAX)
Surge Current	400 A (8/20 us MAX)
Energy	1.6 J (10/1000 us MAX)
Load Dump	3 J
Capacitance	2.35 nF (1kHz)