



Main

| | |
|-----------------------------|----------------------------------|
| Range | Spacial |
| Product name | Spacial S3X |
| Device application | Multi-purpose |
| Product or component type | Compact enclosure |
| Enclosure nominal height | 300 Mm |
| Enclosure nominal width | 250 Mm |
| Enclosure nominal depth | 150 Mm |
| Installation accessory type | Wall-mounting |
| Device composition | 1 body 1 lock: door 1 door |

Complementary

| | |
|-----------------------------|--|
| Body type | Single piece body, cross-shaped structure Gutter shaped front rail |
| Door type | Plain |
| Number of doors | Front face: 1 door(s) |
| Door opening side | Reversible (120 °) |
| Lock type | 3 mm double-bar lock |
| Mounting plate description | Without mounting plate |
| Type of gland plate | Without gland plate |
| Accessibility for operation | Front |
| Removable parts | Door by hinges |
| Material | Body and door: stainless steel 304L Lock: zamak Hinge: stainless steel |
| Surface finish | Body and door: Scotch-Brite® brushed Lock: chromium plated |
| Net weight | 3.53 Kg |

Environment

| | |
|------------------------------|-------------------------------|
| Standards | IEC 62208 |
| Product certifications | UL 508 type A CAN/CSA 22 |
| IP degree of protection | IP66 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |
| Environmental characteristic | Specific hygiene Corrosive |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 3.417 Kg |
| Package 1 Height | 17 Cm |
| Package 1 width | 26 Cm |
| Package 1 Length | 31 Cm |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Product Life Status : **Commercialised**