

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000046](#)
Status: **Active**
Overview: Mini-Fit Jr. Power Connectors
Description: Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 22-28 AWG, Reel

Documents:

Drawing (PDF)	Test Summary 55560000-TS-000 (PDF)
Product Specification PS-5556-001-001 (PDF)	Test Summary 55560010-TS-000 (PDF)
Product Specification PS-5556-002-001 (PDF)	Test Summary TS-5556-002-001 (PDF)
Application Specification 55560001-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification 55560001-PK-000 (PDF)	

General

Product Family	Crimp Terminals
Series	5556
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr. Power Connectors
Packaging Alternative	39000047 (Loose)
Product Name	Mini-Fit
UPC	800753627710

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	123.000/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.80mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Solder Process Data


Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	5556T2
--------------------	--------

Reference - Drawing Numbers

Application Specification	55560001-AS-000
Crimp Specification	CS-5556X2_5558X2
Packaging Specification	55560001-PK-000
Product Specification	PS-5556-001-001, PS-5556-002-001
Sales Drawing	55560000-SD-000
Test Summary	55560000-TS-000, 55560010-TS-000, TS-5556-002-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[5556 Series](#)

Use With

Mini-Fit Jr. Receptacle Housing [5557](#)

Mini-Fit BMI Slide and Lock Panel
Mount [44516](#)
Mini-Fit BMI Panel Mount
Receptacle Housing
 [42474](#) , [43760](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool	11030044
Hand Crimp Tool for Crimp Terminals	638191000
FineAdjust Applicator for Insulation OD 1.30-1.50mm, 22-28 AWG Wire	639002700

FineAdjust Applicator	<u>639020200</u>
for Insulation OD	
1.10-1.30mm - 22-28	
AWG	
FineAdjust Applicator	<u>639023800</u>
for Insulation OD	
0.95-1.08mm - 22-28	
AWG	
T2 Terminator	<u>639102700</u>
for Insulation OD	
1.30-1.50mm, 22-28	
AWG	
T2 Terminator	<u>639120200</u>
for insulation OD	
1.10-1.30mm - 22-28	
AWG	
T2 Terminator	<u>639123800</u>
for insulation OD	
0.95-1.08mm - 22-28	
AWG	
Japan	
Description	Product #
S-1 Applicator	<u>570223720</u>
for Mini-Fit Plug	
and Receptacle	
Terminals, 22-28	
AWG	
Hand Extraction Tool	<u>570316000</u>
Applicator for M21 1A	<u>570383000</u>
Bench Press, 22-28	
AWG Wire	

This document was generated on 04/30/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION