

Search within category **GO**

BUY NOW

DESIGN / INSTALL



HSTT-YK2

Thin wall heat shrink in 6" pieces, black, multiple diameters, .38" - 1" (9.7mm - 25.4mm) diameter, cross-linked polyolefin.

Specs	Packaging Details	Documents
Product Type	Heat Shrink	
Material	Flame Retardant Polyolefin Cross-Linked	
Color	Black	
Flammability Rating	N/A	
Shrink Ratio	2:1	
Temperature Range	-67°F - 275°F (-55°C - 135°C)	
Length (In.)	6.00	
Length (mm)	152.4	
Max. Recovered I.D. (In.)	—	
Max. Recovered I.D. (mm)	NA	
Min. Expanded I.D. (In.)	—	
Min. Expanded I.D. (mm)	—	
Nominal Recovered Wall Thickness (In.)	0.025 - 0.035	
Nominal Recovered Wall Thickness (mm)	0.6	
Military Specification	AMS-DTL-23053/5 Class 1 (material performance only)	
UL Listed	No	
UL Recognized	Yes	
Length (m)	0.1524	
Sub Brand	Dry-Shrink	
RoHS Compliancy Status	Compliant	
Min. Order Qty.	1	

★ Add to Favorites Add to BOM