



# 1522NB

Product no.: 1522NB


Head cutter for 1500 BSF - side cutter - pointed relieved head



This is the narrowest head shape.



The underside is relieved and facilitates optimum access even to extremely hard-to-reach areas.



[source images](#)

## The Perfect Cut - Strong, sharp and precise, every time

1500 Weller Erem pneumatic side cutters are light and precise. Thanks to a selection of different cutting heads they can operate extremely versatile. The cutters are suitable for cutting conventional components, soft metals or small plastic parts. The cutting heads can be interchanged easily.

## THE PERFECT CUT

Strong, sharp and precise - every time

**+ Precision**  
Experience precise cuts from the high-precision screw joint that enables a smooth action with no jaw overlap

**+ Quality**  
Uncompromising Swiss quality created to be strong, durable and sharp

**+ 1 Million Movements**  
Magic Spring™ design enables maximum durability with constant spring force movements

**+ Strong and Sharp**  
Hand-crafted cutting edges for superior strength and sharpness

**+ Comfort, Security and Grip**  
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology

**ESD Safe**  
Made from ESD-safe material to prevent damage to sensitive components

**Swiss Made**

weller-tools.com **Weller**  
Erem





**Technical Data**

Length mm	---
Length of cutting edges mm	9
Head width mm	11
Head thickness mm	6
Head length mm	---
Max. cutting capability – hard wire mm	---
Weight in oz	1.129
Length of cutting edges Inches	0.354
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	---
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	---
Max. cutting capability – copper wire mm	Ø 1,2
Length inches	---
Weight in g	32
Erem applications	Microelectronic