

Section Links

A020 | **A021** | A025

Product Details

A021 Threaded Frame Insert With Stainless Steel Bush For Square Hollow Sections

Materials Bush - Stainless Steel type 303
Moulding - Polyamide Reinforced Nylon



Part No.	Tube Size D1 (mm)	Thread Size D3 (mm)	Internal Dimensions D2 (mm)	Engagement Length H1 (mm)	Shoulder Length H2 (mm)	Threaded Bush Length H3 (mm)	Max Recommended Load (kgs)
A021/001	30 x 30 x 1.5	M10	27	35	8	24	500
A021/002	30 x 30 x 1.5	M12	27	35	8	24	500
A021/003	30 x 30 x 1.5	M16	27	35	8	24	500
A021/004	40 x 40 x 1.5	M10	37	35	8	24	1000
A021/005	40 x 40 x 1.5	M12	37	35	8	24	1000
A021/006	40 x 40 x 1.5	M16	37	35	8	24	1000
A021/007	40 x 40 x 1.5	M20	37	35	8	24	1000
A021/022	40 x 40 x 2.0	M10	36	35	8	24	1000
A021/023	40 x 40 x 2.0	M12	36	35	8	24	1000
A021/014	40 x 40 x 2.0	M16	36	35	8	24	1000
A021/008	40 x 40 x 2.0	M20	36	35	8	24	1000
A021/009	50 x 50 x 1.5	M16	47	45	10	24	1200
A021/010	50 x 50 x 1.5	M20	47	45	10	24	1200
A021/015	50 x 50 x 1.5	M24	47	45	10	24	1200
A021/011	50 x 50 x 2.0	M16	46	45	10	24	1200
A021/012	50 x 50 x 2.0	M20	46	45	10	24	1200
A021/013	50 x 50 x 2.0	M24	46	45	10	24	1200

Dimensions are approximate

