

### SCREW TOGETHER HOODS TOP ENTRY

### DTPK SERIES

#### TECHNICAL SPECIFICATIONS



Material:	UL 94 V-0 Plastic Material
Plating:	Nickel over Copper
Operating Temperature:	-55°C to +110°C
Cable Entry:	Top Entry
Thumbscrews:	UNC 4-40 (standard) M2.5, M2.6 or M3.0 on request
Cable Diameter:	Up to 13 mm

#### FEATURES

- Available in sizes 9-15-25-37
- Suitable for any common Sub-D connector
- Re-openable
- Strain relief inserts ensure a secure termination
- Also available in Unshielded version
- Company logo available upon request
- Recyclable

Size	Product Code
9-way	DTPK9-K
15-way	DTPK15-K
25-way	DTPK25-K
37-way	DTPK37-K

Size	Dim A	Dim B	Dim C
9-way	31,2	39,9	15,0
15-way	39,5	41,5	15,0
25-way	53,4	48,6	15,0
37-way	69,7	53,6	15,0



### SCREW TOGETHER HOODS 45° ENTRY

### D45PK SERIES

#### TECHNICAL SPECIFICATIONS

Material:	UL 94 V-0 Plastic Material
Plating:	Nickel over Copper
Operating Temperature:	-55°C to +110°C
Cable Entry:	Side Entry
Thumbscrews:	UNC 4-40 (standard) M2.5, M2.6 or M3.0 on request
Cable Diameter:	Up to 13 mm

#### FEATURES

- Available in sizes 9-15-25-37
- Suitable for any common Sub-D connector
- Re-openable
- Strain relief inserts ensure a secure termination
- Also available in Unshielded version
- Company logo available on request
- Recyclable

Size	Product Code
9-way	D45PK9-K
15-way	D45PK15-K
25-way	D45PK25-K
37-way	D45PK37-K

Size	Dim A	Dim B	Dim C
9-way	31,0	36,3	15,0
15-way	39,5	40,3	15,0
25-way	53,2	40,3	15,0
37-way	69,7	40,3	15,0

